



Contact assignment:

1	brown
2	white
3	blue
4	black
5	grey

shield connection
flange housing



Minimum wall thickness 1,5mm,
alternativ panel cut-out d=16,1

Technical specification:

Rated voltage: IEC 61076-2-101	60 V
Current rating: IEC 61076-2-101	4 A at 40°C
Insulation resistance: IEC 60512	>=100 MΩ
Pollution degree: IEC 60664-1	3/2
Degree of protection: IEC 60529	IP 67, in mated condition
Temperature range:	-30°C ... +80°C
Mating cycles: IEC 60512-9a	>=100

Materials:

Contact:	CuZn
Contact plating:	Nickel, gold plated
Contact carrier:	PBT GF, UL 94
Sealing:	FPM
Counternut:	CuZn, nickel plated
Socket housing:	CuZn, nickel plated

Installation specification:

Recommended torque:	1-1,2 Nm
Conec installation tool:	Torque wrench: 36-000200 Insert across flats 19: 36-000250

D see data sheet cable

Part no:	Description:	Length L:	Cable:
43-02307	SAL - 12S - FSH5.1 - 0,5 / G3	0,5m	PVC, grey, 5x0,25mm ² flexible installation cable: 781-G32500
43-02355	SAL - 12S - FSH5.1 - 1 / G3	1m	
43-02356	SAL - 12S - FSH5.1 - 2 / G3	2m	
43-xxxxx	SAL - 12S - FSH5.1 - ... / G3	x	

DO NOT ALTER CAD DRAWING BY HAND Directive 2002/95/EC RoHS compliant	dim. in mm		title: Male socket M12x1 with cable, backmounting
	date	name	
	drawn	11.09.13	Brüntrup
	appd.	11.09.13	Fromm
tolerance of cable: L ≤ 4m: L + 40mm L > 4m: L + 1%			dwg no:
general tolerance: 0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm			43K1A2166
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH			part no: see table

CONEC®