



Technical specification/

Technische Daten:

Rated Voltage/ Bemessungsspannung:	250 V AC / 250 V DC
IEC 61076-2-101	
Current rating/ Strombelastbarkeit:	4 A at/ bei 40°C
IEC 61076-2-101	
Insulation resistance/ Isolationswiderstand:	>=100 MΩ
IEC 60512	
Pollution degree/ Verschmutzungsgrad:	3/2
IEC 60664-1	
Degree of protection/ Schutzart:	IP 67, in mated condition/ im verschraubten Zustand
IEC 60529	
Temperature range/ Umgebungstemperatur:	-30°C ... +80°C
Mating cycles/ Steckzyklen:	>=100
IEC 60512-9a	

Materials/

Werkstoffe:

Contact/ Kontakt:	CuZn, Ni b / Au 0,2 gal.
Contact carrier/ Kontaktträger:	PA, UL 94 V-0
Coupling screw/ Überwurfschraube:	GD-Zn, Ni
Moulding body/ Griffkörper:	TPU, UL 94 HB, grey/ grau

Installation specification/

Montagedaten:

Recommended torque/ empfohlenes Drehmoment:	0,6 Nm
Conec	Torque wrench/ Drehmomentschlüssel:
Installation tool/ Montagewerkzeug:	36-000200 Insert across flats 14/ Steckeinsatz SW 14: 36-000370

Contact assignment/


Kontaktbelegung:

1	n.c./ Blindkontakt
2	n.c./ Blindkontakt
3	n.c./ Blindkontakt
4	n.c./ Blindkontakt

Conec part no/ Conec Art.-Nr.:	Description/ Bezeichnung:
43-23945	SAL - 12 - RSA4 / A1029

general tolerance/
Allgemeintoleranz:

0	± 0,50 mm
0,0	± 0,25 mm
0,00	± 0,10 mm
*	± 5 °



dim. in mm

	Date/Datum	Name
drawn/ gez.	18.01.21	Böckeler
appd./ gepr.	18.01.21	Pfeiffer

CONEC®

dwg no /
Z.-nr.:

43K1A5085

DIN-
A4

Index: a Original

Scale/Maßstab:

RoHS compliant/konform

1 / 1