



POS.	A	B	C	D	E	F	Part NO.
9	30.80	16.92	25.00	19.20	11.08	8.31	DLS1XP4AA39X
15	39.20	25.25	33.30	27.70	19.39	16.62	DLS2XP4AA39X
25	53.10	38.96	47.10	41.10	33.24	30.47	DLS3XP4AA39X
37	69.40	55.42	63.50	57.30	49.86	47.09	DLS4XP4AA39X




SEE NOTE 4


Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL * FREIGABE * DEBLOCKAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCKAGE * AUTORIZACION * APPROVAL	

used for: D-SUB



P.C.B. HOLE DRILLINGS




NOTES:

- METALSHELLS: STEEL; min. 320µ" TIN
- INSULATORS: PBT GF UL 94 V-0, BLACK
- CONTACTS: COPPER ALLOY
PLATING: 8µ" HARD GOLD OVER min. 50µ" NICKEL
- CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

1xb	Ä2714	04.06.2007	Son
a	Origin		
rev.	description	date	name

tolerance



scale:

2:1

material:

SEE NOTES

title:

D-SUB MALE

9-37pos. PCB STRAIGHT STAMPED CONTACTS
rear:5.8mm snap-in/front:5.0mm open hex rivet

dwg no:

AutoCAD 2004

DIN-A

16K1A1717

4

sh:1/1

part no:

SEE TABLE

CONEC®