





used for: D-SUB DUAL-PORT



RECOMMENDED P.C.B. LAYOUT
(TOP VIEW)
TOLERANCES: ±0.05mm

NOTES:

1. MATERIAL:

- INSULATOR: THERMAL PLASTIC UL94V-0
- CONTACTS: COPPER ALLOY
- SHELL: STEEL / NICKEL PLATED
- RIVET, BOARDLOCK: COPPER ALLOY

2. CONTACT PLATING:

- UNDERPLATE: 50µin ~ 100µin NICKEL
- CONTACT AREA: GOLD PLATED
- SOLDER TAILS AREA: 100µin ~ 200µin TIN (LEAD FREE)

3. ELECTRICAL:

- OPERATION VOLTAGE: 250 VAC max.
- CURRENT RATING: 3A max.
- CONTACT RESISTANCE: 25 mOhm max.
- INSULATION RESISTANCE: 3000 MOhm min. @ 500 VDC
- DIELECTRIC WITHSTANDING VOLTAGE: 1000 VAC / MINUTE
- TEMPERATURE RANGE: -55°C TO +105°C

4. CONNECTOR IS PART MARKED: PART-NO. CONEC ABC

No. of pos.	A	B	C	Part No.
2x 9	30.8	16.30	25.00	DLS1SS5AN23X
2x15	39.2	24.60	33.30	DLS2SS5AN23X
2x25	53.1	38.30	47.10	DLS3SS5AN23X
2x37	69.4	54.80	63.50	DLS4SS5AN23X

RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

UNLESS OTHERWISE SPECIFIED TOLERANCE			
4 x b	Ä 5932	13.01.2016	Unkrüer
a	Original		
rev.	description	date	name

UNLESS OTHERWISE SPECIFIED TOLERANCE	
0.5 ±0.5	
0.0 ±0.3	
0.00 ±0.2	
2004	date
drawn	11.10. Schmidt
appd.	11.10. Mickenbecker
norm	
d-old	

scale:	2:1
material:	SEE NOTES
title:	
D-SUB DUAL-PORT	
Female / Female 2x9pos. - 2x37pos.	
with 4-40 UNC inserts and clips	
dwg no:	AutoCAD 2000 DIN-A
	16K1A1244 3
part no:	SEE TABLE sh: 1/1