


KM-INOX^{counternut}

stainless steel



KM-INOX

Counternut made of stainless steel.

Material


Stainless steel 1.4305 / AISI 303

Technical data

Temperature range: up to +200°C

Application

- Plant and machine construction
- Robot construction
- Automation technology
- Vehicle construction and shipbuilding
- Rail technology
- Installation technology
- Control cabinet construction



Dimensions

G Thread size inside
SW Spanner size

metric thread - female

Part no.	Size Metr.	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
				up to 100	101 - 500	501 - 1000
920605	M12 x 1,5	15,0	100	o. r.	o. r.	o. r.
920606	M16 x 1,5	19,0	100	o. r.	o. r.	o. r.
920607	M20 x 1,5	24,0	100	o. r.	o. r.	o. r.
920608	M25 x 1,5	30,0	100	o. r.	o. r.	o. r.
920609	M32 x 1,5	36,0	50	o. r.	o. r.	o. r.
920610	M40 x 1,5	46,0	50	o. r.	o. r.	o. r.
920611	M50 x 1,5	60,0	10	o. r.	o. r.	o. r.
920612	M63 x 1,5	70,0	10	o. r.	o. r.	o. r.

PG thread - female

Part no.	Size PG	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
				up to 100	101 - 500	501 - 1000
92970	7	17,0	100	o. r.	o. r.	o. r.
92971	9	19,0	100	o. r.	o. r.	o. r.
92972	11	22,0	100	o. r.	o. r.	o. r.
92973	13,5	24,0	100	o. r.	o. r.	o. r.
92974	16	27,0	100	o. r.	o. r.	o. r.
92975	21	32,0	100	o. r.	o. r.	o. r.
92976	29	41,0	50	o. r.	o. r.	o. r.
92977	36	60,0	25	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request