


HELUTOP® HT-BS Cable gland

with dust protection



HELUTOP® HT-BS

Plastic cable gland with vibration protection and pre-assembled dust protection.

Application

- Plant and machine construction
- Robotics
- Automation technology
- Vehicle construction and shipbuilding
- Railway technology
- Installation technology
- Control cabinet construction

Material

Polyamide PA 6
Seal: Chloroprene-rubber (CR)
Dust protection: foam rubber

- phosphor-free
- silicone-free
- cadmium-free

Properties

- Optimum strain relief through clamping lamella
- Easy to assemble
- Large clamping areas



Note

Details on the individual tests appear in section "Technical Information".
The information of the protection classification applies only by use as cable gland, not as dust cap.

Technical data

Protection class: IP 68 - 5 bar / IP 69K

Temperature range: -20°C up to +100°C



Dimensions

G Thread size
GL Thread length
SW Spanner size

Metric thread

Part no. light grey RAL 7035	Part no. dark grey RAL 7001	Part no. black RAL 9005	Size Metr.	Cable Ø from / to mm	Thread length mm	Spanner size mm	Unit	Net EUR/100 items at a purchase of		
								up to 100	101 - 500	501 - 1000
94530	94540	94550	M12 x 1,5	3,0 - 6,5	8,0	15	100	o. r.	o. r.	o. r.
94531	94541	94551	M16 x 1,5	5,0 - 10,0	10,0	22	50	o. r.	o. r.	o. r.
94532	94542	94552	M20 x 1,5	6,0 - 12,0	10,0	24	50	o. r.	o. r.	o. r.
94533	94543	94553	M25 x 1,5	11,0 - 17,0	8,0	29	25	o. r.	o. r.	o. r.
94534	94544	94554	M32 x 1,5	15,0 - 21,0	10,0	36	25	o. r.	o. r.	o. r.
94535	94545	94555	M40 x 1,5	19,0 - 28,0	10,0	46	20	o. r.	o. r.	o. r.
94536	94546	94556	M50 x 1,5	30,0 - 38,0	18,0	60	10	o. r.	o. r.	o. r.
94537	94547	94557	M63 x 1,5	34,0 - 44,0	18,0	65	10	o. r.	o. r.	o. r.

Dimensions and specifications may be changed without prior notice.

o. r. = on request