









SWITCH FUNCTION	
POS. 1	POS. 2
OFF	ON
OPEN	1-2



- NOTE:
- ALL DIMENSIONS IN MM [INCH]
 - GENERAL TOLERANCE: X.X = ± 0.4
X.XX = ± 0.25
 - TERMINAL NUMBERS FOR REF ONLY
 - CONTACT MATERIAL: SILVER
 - RATING: 20A/250VAC
 - ELECTRIC LIFE: 50,000 MAKE-AND-BREAK CYCLES AT FULL LOAD.
 - INSULATION RESISTANCE: 100M Ω @ 500VDC
 - DIELECTRIC STRENGTH: 1,500 VAC
 - CONTACT RESISTANCE: 50m Ω
 - OPERATING TEMP.: -40°C to 85°C
 - TRAVEL: 3.5mm
 - ▲ DENOTES CRITICAL PARAMETER.
 - LAMP VOLTAGE: 12V
 - ILLUMINATION COLOR: BLUE
 - INGRESS PROTECTION: IP67
 - HARDWARE SUPPLIED: O-RING AND HEXNUT



REV	ECO NO	DESCRIPTION	DATE	BY	E-SWITCH®				OBJECT ID
A	ECO-102939	Release	09/13/24	MW	TITLE PVHC7F23SS644				100128246
					SCALE	DATE	DR	DWG	REV
					3:2	8/14/2024	MW	52-PVHC7F23SS644	A

THE INFORMATION CONTAINED IN THIS DOCUMENT IS PROPRIETARY TO
E-SWITCH AND IS NOT TO BE COPIED OR TRANSFERRED