






THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

CUSTOMER DRAWING



Standard Part List:

Model No.	H+S Part No.	Dia. Primary Insulation(mm)	Dia. of Screen max. (mm)	Overall-Dia. Nominal(mm)	Outside-Dia. of terminal(mm): "A"	Inside-Dia. of terminal(mm): "B"
PL28(X)-30X-35-2-5	84100296	9.7±0.3	10.4	12.7±0.3	12.5±0.3	8.5±0.3
PL28(X)-30X-25-2-5	84100604	8.2±0.3	8.9	11.2±0.3	10.8±0.3	7.3±0.3

REVISIONS

REV#	ECN#	REVISION ACTION	REV.BY:	APPR.BY:	DATE
01	--	INITIAL RELEASE	Star	James	09/04/2020

订购信息 Ordering Information

PL28 X - 30 1 - 25 - 2 -5

Key and Color

"X", Orange
"Y", Black
"U", Yellow
"V", Green
"W", Red
"T", Blue

HVIL

"0", NO HVIL
"1", With HVIL

Cable Size

"25"=25mm²
"35"=35mm²

Cable Type:

"-5", Huber+Suhner

规格参数(Spec.):

- 工作温度 Operating temperature: -40°C ~ +125°C.
- 带高压互锁 Electrical interlock (HVIL).
- 额定电流 Current rating:
Power: 25mm², 120A; 35mm², 150A; HVIL: 5A.
- 额定电压 Operating voltage:
Power: 1000 VDC; Signal: 60 VDC.
- 耐电压 Dielectric withstanding voltage:
A. 与插座对插后, Pin与铁壳之间
When mated, between pin and metal shell: 5000 VDC.
B. 与插座对插后, Pin与HVIL之间
When mated, between pin and HVIL: 5000 VDC.
C. 与插座对插后, HVIL与铁壳之间
When mated, between HVIL and metal shell: 500 VDC.
D. 与插座对插前, 两个HVIL端子之间耐压
Before mating, between two HVIL terminals: 500 VDC.
- 防护等级 Protection class: Mated-IP6k9k & IP67, unmated-IP2X.
- 电磁屏蔽 360° full Shielding.
- 机械寿命 Mating cycle: 100 Min.
- 带CPA摇杆系统 Latch system with CPA.
- 绝缘材料满足UL94 V-0 Inner insulation material satisfy UL94V-0.
- 镀灰锌/镍合金, 符合RoHS, 满足500H中性盐雾实验
Gray Zinc/Nickel(ZnNi) Plating. RoHS compliant, Rated at 500hours salt spray.



Amphenol Technical Products International Asia.

第三角投影 THIRD ANGLE PROJECTION	页 面 SHEET	幅 面 SIZE	版 次 REV.	比 例 SCALE	PART NAME:
	1 OF 2	A4	01		PL10mm G2 1POS Right Angle Plug
签 名 SIGNATURE	日期 DATE	UNLESS OTHERWISE SPECIFIED 1) All dimensions are in metric (mm). 2) Tolerances are as follows: 1. PL DEC ± 1.00 2. PL DEC ± 0.50 3. PL DEC ± 0.20 Angles ± 1°			DWG NO:
制 图 DRAWN	Star	09/04/2020			PL28X-30X-25/35-2-5
审 核 CHECKED					CUST PART #
批 准 APPROVAL					CUST REV.

THIS DRAWING IS SUPPLIED FOR INFORMATION ONLY. DESIGN FEATURES, SPECIFICATIONS AND PERFORMANCE DATA SHOWN HEREON ARE THE PROPERTY OF THE AMPHENOL CORPORATION. NO RIGHTS OF REPRODUCTION ARE IMPLIED. ALL DIMENSIONS ARE SUBJECT TO NORMAL MANUFACTURING VARIATIONS.

1		2		3		4		5		6		7		8	
型号		AC P/N													
PL28X-300-25-2-5		AC-HA016644													
PL28Y-300-25-2-5		AC-HA016645													
PL28U-300-25-2-5		AC-HA016646													
PL28V-300-25-2-5		AC-HA016647													
PL28W-300-25-2-5		AC-HA016648													
PL28T-300-25-2-5		AC-HA016649													
PL28X-301-25-2-5		AC-HA016650													
PL28Y-301-25-2-5		AC-HA016651													
PL28U-301-25-2-5		AC-HA016652													
PL28V-301-25-2-5		AC-HA016653													
PL28W-301-25-2-5		AC-HA016654													
PL28T-301-25-2-5		AC-HA016655													
PL28X-300-35-2-5		AC-HA016656													
PL28Y-300-35-2-5		AC-HA016657													
PL28U-300-35-2-5		AC-HA016658													
PL28V-300-35-2-5		AC-HA016659													
PL28W-300-35-2-5		AC-HA016660													
PL28T-300-35-2-5		AC-HA016661													
PL28X-301-35-2-5		AC-HA016662													
PL28Y-301-35-2-5		AC-HA016663													
PL28U-301-35-2-5		AC-HA016664													
PL28V-301-35-2-5		AC-HA016665													
PL28W-301-35-2-5		AC-HA016666													
PL28T-301-35-2-5		AC-HA016667													