

363BU9

Panel mounted inlet

2CMA167226R1000

Inlet, panel mounting, earthing sleeve position 9h, rated current 63A, IP44 splashproof, unified flange, straight, 3-poles+earth, frequency 50-60 Hz, color code Blue



GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA167226R1000
Function	Inlet, panel mounting, unified flange, straight
EAN	7392696672269
Catalog Description	Inlet, panel mounting, 9h, 63A, IP44, unified flange, straight, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417353
E-Number Norway	2417353
E-Number Sweden	E2417353
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	103 millimetre
Product Net Height	103 millimetre
Product Net Length	126 millimetre
Product Net Depth	126 millimetre
Product Net Weight	0.463 kilogram

TECHNICAL

Product Main Type	TBU
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	63 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	6...25 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Tough&Safe

PACKAGING

Package Width	112 millimetre
Package Height	139 millimetre
Package Gross Weight	0.51 kilogram
Package Length	112 millimetre
Package Units	box 1 piece