

Type No. :

F12S1-□ 210ND □ 000

RoHS
Compliant

□: Material / Finish

S: Stainless Steel

A: Aluminum

P: Brushed Stainless Steel


B: Dark Aluminum

□: Function


1: Momentary

2: Maintained


Dimensions



Electrical Diagram



Panel Cut-out



Terminal	: Solder
Mechanical lifetime	: >50,000 operations
Electrical lifetime	: >50,000 operations
Electric rating	: 48V DC 100mA
Dielectric Strength	: 1000V AC 60Hz 1min.
Insulation Resistance	: 100MΩ
Panel thickness	: 0.5mm~3mm
Degree of protection	: IP67
Operating temperature	: -25°C to 50°C
Contact resistance	: 50mΩ (initial)



DECA® SwitchLab Inc.

PART NAME

UNIT

SCALE

F12S1-x210NDx000

MM

DESIGN

CHECK

APPROVE

DRAWING NO.

SHEET

DATE

DATE

DATE

F12S1-x210NDx000

1/1