

Type No. :

F12S1-□21□□D□001

RoHS
Compliant

Mark 001: Dot

□: Material / Finish

S: Stainless Steel
P: Brushed Stainless Steel

A: Aluminum
B: Dark Aluminum

□: LED Color

G: Green
R: Red
A: Amber
B: Blue
W: White


□: LED Voltage

2: 6V
3: 12V


□: Function

1: Momentary
2: Maintained

Dimensions



Electrical Diagram



Terminal : Solder
Mechanical lifetime : >50,000 operations
Electrical lifetime : >50,000 operations
Electric rating : 48V DC 100mA
Dielectric Strength : 1000V AC 60Hz 1min.
Insulation Resistance : 100MΩ
Panel thickness : 0.5mm~3mm
Degree of protection : IP67
Operating temperature : -25°C to 50°C
Contact resistance : 50mΩ (initial)

DECA[®]SwitchLab Inc.

PART NAME

F12S1-x21xxDx001

UNIT

MM

SCALE

DRAWING NO.

F12S1-x21xxDx001

SHEET

1/1

DESIGN

DATE

2018/05/02

CHECK

DATE

2018/05/02

APPROVE

DATE

2018/05/02

B

REV.