

VIP-CAB-FLK40/FS/NA/HF/ 2,0M - Cable



1116410

<https://www.phoenixcontact.com/gb/products/1116410>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled, shielded, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 40-position, 180 °-out put); connection 2: Single wires (40-position); cable length: 2 m

Commercial data

Item number	1116410
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DK2AH7
Product key	DK2AH7
GTIN	4063151042165
Weight per piece (including packing)	349 g
Weight per piece (excluding packing)	349 g
Customs tariff number	85444290
Country of origin	DE

VIP-CAB-FLK40/FS/NA/HF/ 2,0M - Cable



1116410

<https://www.phoenixcontact.com/gb/products/1116410>

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

Cable/line

Cable length	2 m
UL AWM Style	21946
Number of positions	40
Shielded	yes
Conductor type	Assembled, shielded, halogen-free round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	40x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	9.80 mm ±0.4 mm
Outer sheath, material	Halogen-free sheath
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km
Insulation resistance	≥ 20 MΩ*km
Smallest bending radius, fixed installation	102 mm
Smallest bending radius, movable installation	184 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000
Halogen-free	yes
Flame resistance	IEC 60332-1-2 (raw cable) VDE 0842, Part 332-1-2 (raw cable)

VIP-CAB-FLK40/FS/NA/HF/ 2,0M - Cable



1116410

<https://www.phoenixcontact.com/gb/products/1116410>

	IEC 60332-3-22 (raw cable)
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Color code

black	IDC/FLK50 (1) = IDC/FLK50 (1)
brown	IDC/FLK50 (2) = IDC/FLK50 (2)
red	IDC/FLK50 (3) = IDC/FLK50 (3)
orange	IDC/FLK50 (4) = IDC/FLK50 (4)
yellow	IDC/FLK50 (5) = IDC/FLK50 (5)
green	IDC/FLK50 (6) = IDC/FLK50 (6)
blue	IDC/FLK50 (7) = IDC/FLK50 (7)
violet	IDC/FLK50 (8) = IDC/FLK50 (8)
gray	IDC/FLK50 (9) = IDC/FLK50 (9)
white	IDC/FLK50 (10) = IDC/FLK50 (10)
white-black	IDC/FLK50 (11) = IDC/FLK50 (11)
white-brown	IDC/FLK50 (12) = IDC/FLK50 (12)
white-red	IDC/FLK50 (13) = IDC/FLK50 (13)
white-orange	IDC/FLK50 (14) = IDC/FLK50 (14)
white-yellow	IDC/FLK50 (15) = IDC/FLK50 (15)
white-green	IDC/FLK50 (16) = IDC/FLK50 (16)
white-blue	IDC/FLK50 (17) = IDC/FLK50 (17)
white-violet	IDC/FLK50 (18) = IDC/FLK50 (18)
white-gray	IDC/FLK50 (19) = IDC/FLK50 (19)
brown-black	IDC/FLK50 (20) = IDC/FLK50 (20)
brown-red	IDC/FLK50 (21) = IDC/FLK50 (21)
brown-orange	IDC/FLK50 (22) = IDC/FLK50 (22)
brown-yellow	IDC/FLK50 (23) = IDC/FLK50 (23)
brown-green	IDC/FLK50 (24) = IDC/FLK50 (24)
brown-blue	IDC/FLK50 (25) = IDC/FLK50 (25)
brown-violet	IDC/FLK50 (26) = IDC/FLK50 (26)
brown-gray	IDC/FLK50 (27) = IDC/FLK50 (27)
brown-white	IDC/FLK50 (28) = IDC/FLK50 (28)
green-black	IDC/FLK50 (29) = IDC/FLK50 (29)
green-brown	IDC/FLK50 (30) = IDC/FLK50 (30)
green-red	IDC/FLK50 (31) = IDC/FLK50 (31)
green-orange	IDC/FLK50 (32) = IDC/FLK50 (32)
green-blue	IDC/FLK50 (33) = IDC/FLK50 (33)
green-violet	IDC/FLK50 (34) = IDC/FLK50 (34)
green-gray	IDC/FLK50 (35) = IDC/FLK50 (35)
green-white	IDC/FLK50 (36) = IDC/FLK50 (36)
yellow-black	IDC/FLK50 (37) = IDC/FLK50 (37)
yellow-brown	IDC/FLK50 (38) = IDC/FLK50 (38)
yellow-red	IDC/FLK50 (39) = IDC/FLK50 (39)

VIP-CAB-FLK40/FS/NA/HF/ 2,0M - Cable



1116410

<https://www.phoenixcontact.com/gb/products/1116410>

yellow-orange

IDC/FLK50 (40) = IDC/FLK50 (40)

Connection data

Connection 1

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	40
Exit angle	180 °
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2

Connection method	Single wires
Stripping length (Sheath)	≈  mm
Number of positions	40

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

Drawings

Diagram



Maximum permissible current per path in uncoiled state

VIP-CAB-FLK40/FS/NA/HF/ 2,0M - Cable



1116410

<https://www.phoenixcontact.com/gb/products/1116410>

Classifications

ECLASS

ECLASS-13.0	27242220
-------------	----------

ETIM

ETIM 9.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

VIP-CAB-FLK40/FS/NA/HF/ 2,0M - Cable



1116410

<https://www.phoenixcontact.com/gb/products/1116410>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk