

51730200	DATA SHEET	
Valid from: 20.01.2025	SKINDICHT® VENT	

SKINDICHT® VENT is a pressure compensation element, made of polyamide or stainless steel, with a breathable and waterproof special membrane.



Material:

Gland body	Polyamide / Stainless steel (1.4305)
O-Ring	NBR
Membrane	Acryl-Copolymer

Technical Features:


Connecting thread	M6x0,75 up to M12x1,5 acc. to EN 60423	
Protection class	SKINDICHT® VENT PA	IP66, IP68 and IP69 acc. to EN 60529
	SKINDICHT® VENT INOX	IP66, IP68 and IP69 acc. to EN 60529
	SKINDICHT® VENT PLUS	IP66, IP67 and IP69 acc. to EN 60529
Temperature range	Polyamide	-20°C up to +100°C
	Stainless steel	-40°C up to +105°C

Norm references:




We reserve all rights according to DIN ISO 16016.
PD 0019/05_04.18EN


51730200	DATA SHEET	
Valid from: 20.01.2025	SKINDICHT® VENT	



SKINDICHT® VENT INOX
SKINDICHT® VENT INOX PLUS



SKINDICHT® VENT PA M12
SKINDICHT® VENT PA M12 PLUS



SKINDICHT® VENT PA M6 & M8

Part No.	UL	Colour	Connecting thread	Thread length L mm	Length H mm	Wrench size SW	Air flow 100mbar
SKINDICHT® VENT INOX SKINDICHT® VENT INOX PLUS							
51730204	-	-	M12x1,5	10	21,0	17	0,4 l/min
51730205	Yes	-	M12x1,5	10	21,0	17	2,4 l/min
SKINDICHT® VENT PA SKINDICHT® VENT PA PLUS							
51730188	-	Black (RAL9005)	M6x0,75	10	16,2	10	8 l/std.
51730190	-	Light grey (RAL 7035)	M6x0,75	10	16,2	10	8 l/std.
51730192	-	Grey (RAL 7001)	M6x0,75	10	16,2	10	8 l/std.
51730194	-	Black (RAL9005)	M8x1,0	10	16,2	12	15 l/std.
51730196	-	Light grey (RAL 7035)	M8x1,0	10	16,2	12	15 l/std.
51730198	-	Grey (RAL 7001)	M8x1,0	10	16,2	12	15 l/std.
5173 0200	-	Black (RAL9005)	M12x1,5	10	17,6	17	0,8 l/min
5173 0202	-	Light grey (RAL 7035)	M12x1,5	10	17,6	17	0,8 l/min
5173 0201	Yes	Black (RAL9005)	M12x1,5	10	17,6	17	3,5 l/min
5173 0203	Yes	Light grey (RAL 7035)	M12x1,5	10	17,6	17	3,5 l/min

Creator: MAU1/PDP Released: DAMU1/PDP	Document: DB51730200EN Version: 11	Page 2 of 2
--	---------------------------------------	-------------