









Directive 2002/95/EC
RoHS
Compliant

NOTES:

- HOOD: PBT GF UL 94 V0
- JACKSCREW 4-40 UNC: STEEL; NICKEL PLATED
- SCREW FOR STRAIN RELIEF: STEEL; NICKEL PLATED
- COVER SCREW: STEEL; NICKEL PLATED
- STRAIN RELIEF: STEEL; NICKEL PLATED
- FEMALE CONNECTOR 7W2, CRIMP STYLE WITH WIRE BRIDGE AWG 22
SIGNAL CONTACTS: COPPER ALLOY; 7,5A nominal
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
FEMALE CONTACTS WIRE BRIDGE FROM POS. 1 TO POS. 2

POS. 1



2x JACKSCREW 4-40 UNC
with phillips head

POS. 2



1x CABLE STRAIN RELIEF

POS. 3



2x COVER SCREW

POS. 4



2x CABLE STRAIN RELIEF SCREW

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance
ISO 2768-m



date	name
drawn 30.07.08	Lehmenkühler
appd. 30.07.08	Mickenbecker
norm	
d-old	

CONEC

scale: 2:1
material: SEE NOTES

title:
PLASTIC HOOD, straight cable exit
with 7W2 Female Crimp Connector
with wire bridge and jack screw with phillips head

dwg no: Inventor 10 DIN-A3
13K1A2560 sh: 1

part no: 13-000401