







STRIPPING DIMENSIONS



Directive 2002/95/EC
„RoHS“
Compliant

NOTES:

1. MATERIAL: COPPER ALLOY

2. PLATING:

ITEM 1: NICKEL PLATED

ITEM 2+3: 8µin HARD GOLD over min. 50µin NICKEL

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name

tolerance	
dim. in mm	
drawn	10.12.09 Henneboel
appd.	10.12.09 Koch
norm	
d-old	

CONEC®

scale:	5:1	
material:	SEE NOTES	
title:	HIGH POWER CONTACT MALE CRIMP / SOLDER VERSION 90° - 20A D-SUB COMBINATION	
dwg no:	Inventor	DIN-A3
	13K1A3026	sh: 1
part no:	131A16029X	