






Directive 2002/95/EC
"RoHS"
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

3	1	REAR SIDE	COPPER ALLOY	TIN PLATED							
2	1	MATING SIDE	COPPER ALLOY	min. 30µin HARD GOLD over min. 50µin NICKEL							
1	1	RETAINING RING	COPPER ALLOY	NICKEL PLATED							
item	quantity	part description	material	plating							
partlist											
THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND			tolerance	 dim. in mm	scale:	10:1				
						material:	SEE PARTLIST				
						date	name	title: HIGH POWER CONTACT MALE PREMATING SOLDER PIN / d=3,18mm / 30A D-SUB COMBINATION			
					drawn	02.08.2010	Henneboel				
					appd.	02.08.2010	Fischer				
					norm				dwg no:	Inventor 10	DIN-A3 sh: 1
					d-old						
		a	Origin								
		rev.	description	date	name			part no:		131C12149X	