




NOTES:

1. MATERIAL:

ITEM 1+2: COPPER ALLOY

ITEM 3: STAINLESS STEEL


2. PLATING:

ITEM 1: SEE TABLE

ITEM 2: TIN PLATED

PLATING ITEM 1	PART-NO.
GOLD FLASH over NICKEL	131A13160X
30µm GOLD FLASH over 50µm NICKEL	131C13160X

Directive 2011/65/EU RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance			 dim. in mm	scale: 5:1	
									material: SEE NOTES	
						date	name	title: HIGH POWER CONTACT MALE SOLDER PIN 90°, Ø 2,85 , 20A, PREMATING D-SUB COMBINATION		
					drawn	28.03.2014	Henneboel			
					appd.	31.03.2014	Lehmenkühler			
					norm					
					d-old					
								dwg no: 13K1A4621		DIN- A4
	a	Original								
	rev.	description	date	name				part no: SEE TABLE		sh: 1