


4

3

2

1

used for: D-SUB COMBINATION



NOTES:

1. MATERIAL: COPPER ALLOY

2. PLATING:

ITEM 1: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL

ITEM 2: min. 8µ" HARD GOLD OVER min. 50µ" NICKEL


ITEM 3: NICKEL PLATED

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACON # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

2 x c	Ä 1615	21.08.2002	Parei
1 x b	Ä 1603	08.08.2002	Parei
rev.	description	date	name

tolerance
ISO 2768-m



2002	date	name
drawn	26.07.	Parei
appd.	26.07.	E. Mickenbecker
norm		
d-old		

CONEC®

scale: 5:1
material: SEE NOTES

title:
HIGH POWER CONTACT MALE
(b) CRIMP / SOLDER VERSION 90° - 20A
D-SUB COMBINATION

dwg no: AutoCAD DIN-A
13K1A659 4
sh: 1/1
part no: 131C16029X

4

3

2

1