


4

3

2

1

used for: D-SUB COMBINATION



Directive 2002/95/EC
„RoHS“
Compliant

NOTES:

1. MATERIAL: COPPER ALLOY

2. PLATING:

ITEM 1: min. 30µ" HARD GOLD OVER min. 50µ" NICKEL

ITEM 2: TIN PLATED


ITEM 3: NICKEL PLATED

3. PCB-THICKNESS: min. 1.6mm


Ø PCB-HOLE: 3.02mm min. / 3.20mm max.

APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACIION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCKAGE # AUTOR/ZACIION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

				tolerance		 dim. in mm
				ISO 2768-m		
				2003	date	name
				drawn	30.10.	Lehmenkühler
				appd.	30.10.	Mickenbecker
				norm		
				d-old		
						
rev.	description	date	name			

CONEC®



scale: 5:1
material: SEE NOTES

title:
HIGH POWER CONTACT MALE
PRESSFIT VERSION 30A
D-SUB COMBINATION

dwg no: AutoCAD 2000 DIN-A
13K1A978 4
sh: 1/1

part no: 131C19019X

4

3

2

1