



used for:	D-SUB COMBINATION
-----------	-------------------



Directive 2002/95/EC
„RoHS“
Compliant

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
	CUSTOMER APPROVAL DATE:	
	NAME:	TITLE:
	COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	


NOTES:

1. MATERIAL:
ITEM 1-5: COPPER ALLOY
ITEM 6: STAINLESS STEEL
2. PLATING:
ITEM 1: min. 30µin HARD GOLD OVER min. 50µin NICKEL
ITEM 2-5: NICKEL PLATED

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.

OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

				tolerance ISO 2768-m		 dim. in mm	
				2009	date	name	
				drawn	01.12.	Lehmenkühler	
				appd.	01.12.	Koch	
				norm			
				d-old			
							
a	Origin						
rev.	description	date	name				

scale:	5:1
material:	SEE NOTES

title: HIGH POWER CONTACT MALE Screw Termination for AWG 14, 20A PREMATING CONTACT / D-SUB COMBINATION
--

dwg no:	AutoCAD 2006	DIN-A
13K1A3014		4
		sh: 1/1

part no:	131C36109X
----------	------------