




## NOTES:

### 1. MATERIAL:

ITEM 1+2: COPPER ALLOY

ITEM 3: STAINLESS STEEL

### 2. PLATING:

ITEM 1: SEE TABLE

ITEM 2: TIN PLATED

| PLATING ITEM 1                       | PART-NO.   |
|--------------------------------------|------------|
| 8µ" HARD GOLD OVER min. 50µ" NICKEL  | 132A13060X |
| 30µ" HARD GOLD OVER min. 50µ" NICKEL | 132C13060X |

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR  
REPRODUCED IN ANY WAY, AND MAY NOT  
BE PASSED ON TO A THIRD PARTY WITHOUT  
WRITTEN PERMISSION.  
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

|      |             |      |      | tolerance     |            | dim. in mm   |
|------|-------------|------|------|---------------|------------|--------------|
| rev. | description | date | name |               |            |              |
| a    | Original    |      |      |               |            |              |
|      |             |      |      | drawn         | 22.06.2004 | Schmidt      |
|      |             |      |      | appd.         | 22.06.2004 | Mickenbecker |
|      |             |      |      | norm          |            |              |
|      |             |      |      | d-old         |            |              |
|      |             |      |      | <b>CONEC®</b> |            |              |

|           |                                                                                       |        |
|-----------|---------------------------------------------------------------------------------------|--------|
| scale:    | 5:1                                                                                   |        |
| material: | SEE NOTES                                                                             |        |
| title:    | <b>HIGH POWER CONTACT FEMALE</b><br>SOLDER PIN 90°, Ø 2,85 , 20A<br>D-SUB COMBINATION |        |
| dwg no:   | 13K1A1157                                                                             | DIN-A4 |
| part no:  | SEE TABLE                                                                             |        |
|           |                                                                                       | sh: 1  |