




SPL (HONG KONG) LIMITED

香港九龍觀塘鴻圖道57號南洋廣場17樓1703B室
Room 1703B, 17/F., Nanyang Plaza, No.57 Hung To Road, Kwun Tong, Kowloon, HK.
Tel: 852-2342 6857 / 2342 6867 Fax: 852-2342 6847 Email: sales@spl-hk.com.hk
Website: www.buzzer.com.hk

External Drive Piezo Transducer SPT91 series

DIMENSIONS

Date : 15 May, 2025



Ref No. : PBED2903B



ELECTRICAL SPECIFICATIONS

Model No.	PT91-120320LMYR
Sound Pressure Level	72 dBA min. [12 Vp-p square wave, 10cm, 2000Hz]
Capacitance	20000 pF $\pm$ 30% at 100Hz
Max. Input Voltage	25 Vp-p
Heat Test	Must Be Normal [85 $\pm$ 3 $^{\circ}\text{C}$, 24 Hours]
Cold Test	Must Be Normal [-40 $\pm$ 3 $^{\circ}\text{C}$, 24 Hours]
Humidity Test	40 $\pm$ 3 $^{\circ}\text{C}$, 92 ~ 95% R.H. 24 Hours
Operating Temperature [$^{\circ}\text{C}$]	-40 ~ +185
Storage Temperature [$^{\circ}\text{C}$]	-40 ~ +85
Terminal	LCP
Housing Material	SMD
Colour	Black
Weight [gm]	Approx. 0.4 g