






NOTES: (b)

- METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- METAL BRACKETS: ZINC DIE CAST; 300µm COPPER/40-120µm NICKEL/120-200µm TIN
- THREADED LOCKS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
- FIXING-PLATE: PBT GF UL 94 V-0; BLACK
- P.C.B. HOLE DRILLINGS ON SHEET 2
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 163A16539X CONEC ABC


Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale:	2:1 (5:1)				
							material:	SEE NOTES				
								date	name	title: D-SUB MALE 90° 25pos. SOLDER PIN ANGLED 0.318inch threaded lock and metal bracket		
								drawn 24.03.2004	Mankopf			
								appd. 24.03.2004	Mickenbecker			
				norm		dwg no:			DIN- A3 sh: 3/6			
				d-old								
3 x b	Ä036	07.07.2011	K.H.			16K1A1129						
a	Original											
rev.	description	date	name									
						part no:			163A16539X			

DIN-A3
sh: 3/6

P.C.B. HOLE DRILLINGS

(P.C.B. TOP SIDE)



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH										tolerance				 dim. in mm	scale: 2:1																																																																																																																																																																																																																																																																																																																																									
															material: SEE SHEET3																																																																																																																																																																																																																																																																																																																																									
															date	name	title: P.C.B. HOLE DRILLINGS D-SUB Male 25pos. 0.318inch with threaded lock and metal bracket																																																																																																																																																																																																																																																																																																																																							
										drawn	04.07.11	Henneboel																																																																																																																																																																																																																																																																																																																																												
													appd.	04.07.11	Koch																																																																																																																																																																																																																																																																																																																																									
										norm																																																																																																																																																																																																																																																																																																																																														
											d-old																																																																																																																																																																																																																																																																																																																																													
														dwg no:		DIN-A3																																																																																																																																																																																																																																																																																																																																								
a	Original																																																																																																																																																																																																																																																																																																																																																							