





NOTES:

1. METAL SHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY; PLATING (SEE PART NO):
 - PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
 - PLEASE ADD B for 20µm HARD GOLD over min. 50µm NICKEL
 - PLEASE ADD C for 30µm HARD GOLD over min. 50µm NICKEL
4. THREADED REAR SPACERS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
5. SLEEVES: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
6. P.C.B. HOLE DRILLINGS ON SHEET 2
7. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
8. CONNECTOR IS PART MARKED: 164□12069X CONEC ABC

ROHS compliant, exemption 6c/
ROHS konform, Ausnahme 6c


THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

a	Original		
rev.	description	date	name

CONEC®

scale: 2:1 (5:1)	
material: SEE NOTES	
title: D-SUB FEMALE 50pos. SOLDER PIN STRAIGHT with threaded rear spacer	
dwg no:	DIN-A3
16K1A3107	sh: 1/2
part no: 164□12069X (see note 3)	



THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH	DO NOT ALTER CAD DRAWING BY HAND				tolerance			scale:	3:1
					0 ± 0,50 mm 0,0 ± 0,25 mm 0,00 ± 0,10 mm ± 1,5°	dim. in mm		material:	SEE SHEET 1
					date	name		title: P.C.B. HOLE DRILLINGS D-SUB FEMALE 50pos. SOLDER PIN STRAIGHT with threaded rear spacer	
					drawn 18.09.2012	Henneboel			
					appd. 18.09.2012	Fischer			
					norm				
					d-old		dwg no: 16K1A3107		
	a	Original					DIN-A3 sh: 2/2		
	rev.	description	date	name					
						part no: SEE SHEET 1			

CONEC®