






NOTES:

1. METAL SHELLS: STEEL; min. 320 μ " TIN
2. INSULATORS: PBT GF UL 94 V-0, BLACK
3. CONTACTS: COPPER ALLOY
4. PLATING: min. 8 μ " HARD GOLD OVER min. 50 μ " NICKEL
5. METAL BRACKET: STEEL; min. 320 μ " TIN over 80 μ " NICKEL
6. THREADED LOCK: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
7. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
8. = CRITICAL DIMENSION: SPC



THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH
DO NOT ALTER CAD DRAWING BY HAND

tolerance				name	
				A. Mickenbecker	
2000		date		25.07.	
drawn		25.07.		E. Mickenbecker	
appd.		norm		DIN 4 1652	
d-old					



used for: D-SUB Dual-Port