



1. METAL SHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; BLACK
3. CONTACTS: COPPER ALLOY; PLATING (SEE PART NO.):
 - PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
 - PLEASE ADD B for 20µin HARD GOLD over min. 50µin NICKEL
 - PLEASE ADD C for 30µin HARD GOLD over min. 50µin NICKEL
 - PLEASE ADD J for 50µin HARD GOLD over min. 50µin NICKEL
4. THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
5. COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
6. MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
7. CONNECTOR IS PART MARKED: 164□17069X CONEC ABC (see note 3)



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GMBH				DO NOT ALTER CAD DRAWING BY HAND				tolerance						scale: 2:1 (5:1)	
												dim. in mm		material: see notes	
						date	name		title: D-SUB HD FEMALE 26pos. SOLDER CUP with threaded insert						
					drawn	20.11.13	Schmidt								
					appd.	20.11.13	Lehmenkühler								
					norm										
					d-old	16K1A989			dwg no:				DIN-A3 sh: 1		
1 x b	Ä5006	20.11.13	HS												
a	Original														
rev.	description	date	name						part no: 164□17069X (see note 3)						