








NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; BLACK
- CONTACTS: COPPER ALLOY; PLATING (SEE PART NO.):
☐ PLEASE ADD A for GOLD FLASH over NICKEL (PREFERRED TYPE)
☐ PLEASE ADD B for 20µin HARD GOLD over min. 50µin NICKEL
☐ PLEASE ADD C for 30µin HARD GOLD over min. 50µin NICKEL
☐ PLEASE ADD J for 50µin HARD GOLD over min. 50µin NICKEL
- THREADED INSERTS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- COLLARS: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 164□17079X CONEC ABC (see note 3)

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			scale: 2:1 (5:1)			
				dim. in mm			material: see notes			
								date	name	title: D-SUB HD FEMALE 44pos. SOLDER CUP with threaded insert
								drawn 20.11.13	Schmidt	
								appd. 20.11.13	Lehmenkühler	
								norm		
								d-old	16K1A989	
1 x b	Ä5006	20.11.13	HS			dwg no:	DIN-A3			
a	Original					16K1A3351	(b)	sh: 1		
rev.	description	date	name			part no:	164□17079X (see note 3)			