






used for: D-SUB COMBINATION CRIMP



NOTES:

1. METAL SHELLS: STEEL; min. 315µin TIN OVER 40-80µin NICKEL
2. INSULATORS: PBTP GF UL 94 V-0, BLACK
3. CONNECTOR IS PART MARKED: 3005W1SXX99A10X CONEC ABC

Directive 2002/95/EC
RoHS
Compliant

APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL * FREIGABE * DEBLOCAGE * AUTORIZACION * APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH
DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance		
2006	date	name
drawn	23.11.	Schwenkler
appd.	23.11.	Lehmenkühler
norm		
d-old		

scale:	2:1 (5:1)
material:	SEE NOTES
title: D-SUB COMBINATION FEMALE 5W1S CRIMP STYLE	
dwg no:	AutoCAD 20006
13K1A1899	
part no: 3005W1SXX99A10X	

DIN-A
3
sh: 1/1