

RoHS Compliant

REV	SIGN	DATE	DESCRIPTION	APPROVER
B		07/12-18	Initial release	Chen Bo




THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

Material:

- Item ㉓ Terminal(housing):Thermoplastic (UL94 V-0)
- Item ㉔ Contact pin: Brass,Bright Tin plated over Nickel plated

Electrical:

- Voltage rating: 300V
- Current rating: 10A
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- Wave soldering temperature: 260°C±5°C/5 Sec
- Safety Approval:
- Critical dimension: ▲



P.C.B. LAYOUT

OP xx 6 3 x x xxxx G

POLES

02 2pole
02 3pole
...
12 12pole

G RoHS compliant
(lead<4%)
In copper Alloy
0000: Standard
Any special item by
customer request.
please contact sales
department.

0 PA66

0 Bright Tin plated over Nickel plated

DIMENSION

Dim A	N×8.0
Dim B	(N-1)×8.0

N = Number of poles

Poles	Tolerance
2P-4P	±0.15
5P-7P	±0.20
8P-10P	±0.30
11P-12P	±0.40

Amphenol
ANYTEK**CUSTOMER COPY**

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	OP-8.0mm series							
PART NO.	OPxx63xxxxxxG			DWG NO.	80P0301			
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.				Tolerance
		Chen Bo 07/12-18	Chen Bo 07/12-18		UNIT: mm	X.	±0.50	
					SCALE: NONE	X.X	±0.30	
					REV: B	X.XX	±0.10	
					SHEET: 01/01		X°	±1°