





RoHS Compliant



N = Number of poles
Dim.L=N×10.16
Dim.B=(N-1)×10.16

POLES	Dim.L
3P	±0.15
5P/7P	±0.25
9P/11P	±0.35

VP xx 6 5 x 7 xxxx G			
No. OF POLES	Color	0000:"@ "Logo (Standard)	RoHS compliant
03 3 POLES	0 Black (RAL9005)	000A:"ANYTEK" Logo	(lead<4%)
05 5 POLES	2 Red (RAL3001/D)	Any special item by	In copper Alloy
...	3 Orange(RAL2011/P)	customer request,	
...	4 Yellow(RAL1018/A)	please contact sales	
...	5 Green(RAL6018/T)	department.	
11 11 POLES	6 Blue (RAL5015/A)		
	8 Grey(RAL7035/D)		
	9 White(RAL1102)		
	C Green(RAL6018/U)		

Rev.	SIGN	DATE	DESCRIPTION	APPROVER
B	—	8/16'22	The first release	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!


Material:

- Item① Terminal housing :Thermoplastic (UL 94V-0)
 - Item② Clamp : Steel stamping , Zinc plated
 - Item③ Wire guard solder pin : Copper , Bright Tin plated over Nickel plated.
 - Item④ Terminal screw: Steel Zinc plating"- "slot type
- | | | |
|--------------------------------|---|--|
| Electrical | cULus | VDE |
| ● Voltage rating : | 300V | 750V |
| ● Current rating : | 65A | 76A |
| ● Wire range : | | 0.5-16mm ² (Rigid solid&stranded) |
| ● Flexible wire: | | 0.5-10mm ² (Flexible) |
| ● Solid wire (AWG) : | 6-20 | |
| ● Stranded wire (AWG) : | 6-20 | |
| ● Torque : | 19 Lb-In | 1.8N.m |
| ● Screw : | M4.5 | |
| ● Wire strip length : | 10~11mm | |
| ● Withstanding voltage : | 1.6KV / 3.0KV | |
| ● Operating temperature : | -40°C to +115°C | |
| ● Wave Soldering temperature : | 260°C±5°C/5 Sec | |
| ● Safety Approval : | CE, UL, VDE | |
| ● Critical dimension: ▲ | | |
| ● Reference dimension: (×) | The dimensions of pitch are just for reference,take the actual assembly result as a judgment when inserting the terminal block into the PCB hole. | |




Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VP 10.16 Series (pitch=4.00 Double contact)(Odd number of poles)奇数pole						
PART NO.	VPxx65x7xxxxG			DWG NO.	8VP0502		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Guoxue 2022.08.16	Guoxue 2022.08.16		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
				SHEET: 01/01		REV.: B	X.XX ±0.10

RoHS Compliant



Material:

- Item① Terminal housing :Thermoplastic (UL 94V-0)
 - Item② Clamp : Steel stamping , Zinc plated
 - Item③ Wire guard solder pin : Copper , Bright Tin plated over Nickel plated.
 - Item④ Terminal screw: Steel Zinc plating"-slot type
- | Electrical | cULus | VDE |
|--|---|--|
| ● Voltage rating : 300V | | 750V |
| ● Current rating : 65A | | 76A |
| ● Wire range : | | 0.5-16mm ² (Rigid solid&stranded) |
| ● Flexible wire: | | 0.5-10mm ² (Flexible) |
| ● Solid wire (AWG) : 6-20 | | |
| ● Stranded wire (AWG) : 6-20 | | |
| ● Torque : 19 Lb-In | | 1.8N.m |
| ● Screw : M4.5 | | |
| ● Wire strip length : 10~11mm | | |
| ● Withstanding voltage : 1.6KV / 3.0KV | | |
| ● Operating temperature : -40°C to +115°C | | |
| ● Wave Soldering temperature : 260°C $\pm$ 5°C/5 Sec | | |
| ● Safety Approval : cULus VDE | | |
| ● Critical dimension: ▲ | | |
| ● Reference dimension: (×) | The dimensions of pitch are just for reference,take the actual assembly result as a judgment when inserting the terminal block into the PCB hole. | |

N = Number of poles

Dim L=N $\times$ 10.16

Dim B=(N-1) $\times$ 10.16


POLES	Dim L
2p	± 0.15
4p	± 0.15
6P/8P	± 0.25
10P/12P	± 0.35

VP xx 6 5 x 7 xxxx G			
No. OF POLES	Color	0000:"@ "Logo (Standard)	RoHS compliant (lead<4%) In copper Alloy
02 2 POLES	0 Black (RAL9005)	000A:"ANYTEK"Logo	
04 4 POLES	2 Red (RAL3001/D)	Any special item by customer request, please contact sales department.	
...	3 Orange(RAL2011/P)		
...	4 Yellow(RAL1018/A)		
12 12 POLES	5 Green(RAL6018/T)		
	6 Blue (RAL5015/A)		
	8 Grey(RAL7035/D)		
	9 White(RAL1102)		
	C Green(RAL6018/U)		

Amphenol
ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	VP 10.16 Series (pitch=4.00 Double contact)(Even number of poles)偶數 Pole						
PART NO.	VPxx65x7xxxxG			DWG NO.	8VP0503		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Guoxue 2022.08.16	Guoxue 2022.08.16		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
					SHEET: 01/01		X.XX ±0.10
					REV.: B		X° ±1°