









P.C.B. HOLE DRILLINGS
(P.C.B. TOP SIDE)



NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0; GREEN
- SIGNAL CONTACTS: COPPER ALLOY;
PLATING: GOLD FLASH over NICKEL
- COAXIAL CONTACTS 50 OHM: COPPER ALLOY;
PLATING, INNER CONDUCTOR: 50µin HARD GOLD over min. 50µin NICKEL
PLATING, OUTER CONDUCTOR: MATING AREA: 30µin HARD GOLD over min. 50µin NICKEL
TERMINATION SIDE: GOLD FLASH over NICKEL
- CONNECTOR IS PART MARKED: **3007W2PAR76A10X CONEC ABC**



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance			scale: 2:1 (5:1)						
							material: SEE NOTES						
								date	name	title: D-SUB COMBINATION MALE 7W2P			
								drawn	03.02.14				Henneboel
								appd.	03.02.14				Schmidt
								norm		dwg no: 13K1A4570			
								d-old					
											sh: 1		
				a	Original								
				rev.	description	date	name	part no: 3007W2PAR76A10X					