









P.C.B. HOLE DRILLINGS



SEE NOTE 7



Directive 2002/95/EC
"RoHS"
Compliant

NOTES:

- METALSHELLS: STEEL; min. 315µin TIN over 40-80µin NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: 8µin HARD GOLD over min.. 50µin NICKEL
- COAXIAL CONTACTS 50 OHM: COPPER ALLOY
PLATING INNER CONNECTOR: 50µin HARD GOLD over min. 50µin NICKEL
PLATING OUTER CONNECTOR: 30µin HARD GOLD over 50µin NICKEL
- THREADED SPACER CLIP: COPPER ALLOY; min. 200µin TIN over 80µin NICKEL
PCB-HOLE: Ø3,1 ± 0,1; PCB THICKNESS 1,6mm
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3007W2PAR76E20X CONEC ABC

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm
date	name
drawn	29.08.2007 Sonnenberg
appd.	29.08.2007 Mickenbecker
norm	
d-old	

CONEC

scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB COMBINATION MALE 7W2P with treaded spacer clip
dwg no:	Inventor 10
	13K1A2218
part no:	3007W2PAR76E20X

DIN-
A3
sh: 1