




SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



MATERIALS ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 20 A
 WITHSTAND VOLTAGE: AC 2000 V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 7 Lb-In.
 WIRE RANGE: 22 - 12 AWG
 1) MOLDED PARTS: Thermoplastic (UL 94 V-0)
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M3
 4) COVER MATERIAL: PC
 APPROVAL: us
 Critical dimension:

YK 403 xx 1 x x 00G

NO. OF POLES
 02: 2 POLES
 03: 3 POLES

RoHS compliant
 (lead<4%) In copper Alloy
 MARK
 0: "@ " MAK
 1: "ANY" MAK

TERMINAL & SCREW PLATED
 0: TERMINAL & SCREW: G/F
 1: TERMINAL: G/F, SCREW: Zinc
 2: TERMINAL: Sn, SCREW: G/F
 3: TERMINAL: Sn, SCREW: Zinc

N = Number of poles




DIM	TOL
Dim L	(N+1)×8.25+8.3 ±0.30
Dim P	(N-1)×8.25 ±0.30
Dim B	(N+1)×8.25 ±0.30

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-403 With Flange&With Cover Series (2P-3P)						
PART NO.	YK403xx1xx00G			DWG NO.	8YK0015-403		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	Tolerance		
		Guoxue 2014.06.11	Guoxue 2014.06.11		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
						X.XX	±0.10
						X°	±1°
				SHEET: 01/01	REV.: B		



N = Number of poles Δ

DIM		TOL				
		4P	5P-8P	9P-16P	17P-23P	24P-30P
Dim L	$(N+1) \times 8.25 + 8.3$	± 0.30	± 0.40	± 0.50	± 0.60	± 0.80
Dim P	$(N-1) \times 8.25$	± 0.30	± 0.40	± 0.50	± 0.60	± 0.80
Dim B	$(N+1) \times 8.25$	± 0.30	± 0.40	± 0.50	± 0.60	± 0.80

SIGN	DATE	DESCRIPTION	APPROVER
Δ	2007.09.18	Demention changed from $(N \times 8.25) \pm 0.80$ to $(N+1) \times 8.25 + 8.3 \pm 0.80$	Steady
Δ	2007.09.18	The Dimension 15.4 is added	Steady
Δ	08/16`11	The Dimension 6.25 & 7.25 & Dim B & 12.4 & 6.5 are added	Chen Bo
Δ	08/23`11	DWG NO is changed	Chen Bo
Δ	11/03`12	Change the screw plating specification	Jacky
Δ	06/03`14	change the structure	Guoxue
Δ	06/03`14	Change the dimensional tolerance	Guoxue
Δ	07/12`14	Update the drawing	Evan
Δ	08/25`14	The dimensional tolerance is changed from 15.4 ± 0.30 to 15.4 ± 0.50	Airy min
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

300 V, 20 A

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 M Ω OR MORE AT DC 500 V

OPERATING TEMPERATURE RANG:

-40 °C ~ +115 °C

SCREW TORQUE VALUE:

7 Lb-In.

WIRE RANGE:

22 - 12 AWG

1) MOLDED PARTS:

Thermoplastic (UL 94 V-0)

2) TERMINAL:

BRASS, 0.8t

3) TERMINAL SCREWS:

STEEL, M3

4) COVER MATERIAL:

PC

APPROVAL: 

Critical dimension: ∇

YK 403 xx 1 x x 00G

NO. OF POLES

04: 4 POLES

05: 5 POLES

06: 6 POLES

...

30: 30 POLES

RoHS compliant
(lead<4%)

MARK

0: "@ " MAK

1: "ANY" MAK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

Δ 1: TERMINAL: G/F, SCREW: Zinc


2: TERMINAL: Sn, SCREW: G/F

Δ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-403 With Flange&With Cover Series (4P-30P)				
PART NO.	YK403xx1xx00G			DWG NO.	8YK0003-403 Δ	
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		
		Airy min 2014.08.25	Airy min 2014.08.25		UNIT: mm	X. ± 0.50
					SCALE: NONE	X.X ± 0.30
						X.XX ± 0.10
						X° $\pm 1^\circ$
SHEET: 01/01		REV.: H				