









COAXIAL CONTACTS



NOTES:

- METALSHELLS: STEEL; min. 315µm TIN over 40-80µm NICKEL
- INSULATORS: PBT GF UL 94 V-0, GREEN
- SIGNAL CONTACTS: COPPER ALLOY
PLATING: GOLD FLASH over NICKEL
- COAXIAL CONTACTS 50 OHM: COPPER ALLOY
PLATING, INNER CONDUCTOR: 50µm HARD GOLD over min. 50µm NICKEL
PLATING, OUTER CONDUCTOR: MATING AREA: 30µm HARD GOLD over min. 50µm NICKEL
TERMINATION SIDE: GOLD FLASH over NICKEL
- METAL BRACKETS: ZINC DIE CAST; 300µm COPPER/ 40-120µm NICKEL/ 120-200µm TIN
- THREADED INSERTS: COPPER ALLOY; min. 200µm TIN over 80µm NICKEL
- MAXIMUM TORQUE VALUE FOR THREAD: 6 in.LB
- CONNECTOR IS PART MARKED: 3007W2SAT78N20X CONEC ABC



Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH				tolerance		 dim. in mm	scale: 2:1 (5:1)					
							material: SEE NOTES					
								date	name	title: D-SUB COMBINATION FEMALE 7W2S with threaded insert and metal bracket		
								drawn	15.08.2014			Heinrich
								appd.	15.08.2014			Lehmenkühler
								norm				
								d-old				
										dwg no: 13K1A4747		DIN-A3 sh: 1
				a	Original							
				rev.	description	date	name					
DO NOT ALTER CAD DRAWING BY HAND						part no: 3007W2SAT78N20X						

CONEC