






N = Number of poles
 Dim A = $N \times 9.5 + 1.5$
 Dim B = $(N - 1) \times 9.5$

Poles	Tol.	Dim A & B
2-4p		± 0.20
5-8p		± 0.25
9-16p		± 0.35
17-23p		± 0.40
24-30p		± 0.50

SIGN	DATE	DESCRIPTION	APPROVER
△	10/20'08	Add APPROVAL: CQC	Kind
△	4/17'09	Explanation changed	Eris
△	06/04'11	Critical dimension is changed.	Tason
△	06/04'11	The Wire Range is changed from 20-14AWG to 22-14AWG	Tason
△	06/04'11	The tolerance table is changed.	Tason
△	06/16'11	The dimension is changed from 5.56 to 5.5	Tason
△	06/16'11	The dimension is changed from 1.6 to 1.5	Tason
△	11/10'12	Change the screw plating specification	Jacky
△	12/23'13	Change the withatand voltage , current, Screw Torque.	Guoxue

THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!

MATERIALS ELECTRICAL	cULus	CQC
2 RATED VOLTAGE & CURRENT:	300 V, 30A	/ 300V 24A 9
WITHSTAND VOLTAGE:	AC2500V/min	△
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V	
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C	
SCREW TORQUE VALUE:	10.54 Lb-In.	/ 0.8Nm 9
2 WIRE RANGE:	22 - 10 AWG	/ 22-14 AWG △
1) MOLDED PARTS:	Thermoplastic, UL 94 V-0 BLACK	
2) TERMINAL:	BRASS, 0.8t, Tin PLATED	
3) TERMINAL SCREWS:	STEEL, M3.5	
4) Flange:	Thermoplastic, UL 94 V-0 BLACK	
3 Critical dimension:		
1 APPROVAL:	cULus	CQC

YK 443 xx 3 x x 00G G:RoHS compliant
 (lead<4%)
 in copper alloy
 MARK 0: "@" MARK
 1: "ANY" MARK

NO. OF POLES	TERMINAL & SCREW PLATED
02: 2 POLES	0: TERMINAL & SCREW: G/F
03: 3 POLES	1: TERMINAL: G/F, SCREW: Zinc
04: 4 POLES	2: TERMINAL: Sn, SCREW: G/F
...	3: TERMINAL: Sn, SCREW: Zinc
30: 30 POLES	

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-443 Series						
PART NO.	YK443xx3xx00G			DWG NO.	8YK0001-443		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Guoxue 2014.01.07	Guoxue 2014.01.07		UNIT: mm	X. ±0.50	
					SCALE: NONE	X.X ±0.30	
				SHEET: 01/01	REV.: J	X.XX ±0.10	
						X° ±1°	