





SIGN	DATE	DESCRIPTION	APPROVER
△			
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			



N=Number of contacts
Dimension A&B

DIM A	N×9.5+3.0
DIM B	(N-1)×9.5

Poles	Tolerance
2P-3P	±0.20

MATERIALS ELECTRICAL
 RATED VOLTAGE & CURRENT: 300 V, 20 A
 WITHSTAND VOLTAGE: AC 2000 V/Min
 INSULATION RESISTANCE: 1000 MΩ OR MORE AT DC 500 V
 OPERATING TEMPERATURE RANG: -40 °C ~ +115 °C
 SCREW TORQUE VALUE: 12 Lb-In.
 WIRE RANGE: 22 - 12AWG
 1) MOLDED PARTS: THERMOPLASTIC, UL 94 V-0 BLACK
 2) TERMINAL: BRASS, 0.8t
 3) TERMINAL SCREWS: STEEL, M3.5
 4) COVER MATERIAL: PC
 APPROVAL: us
 Critical dimension:
 PART No.:

YK501 xx 2 x x 00G

NO. OF POLES
 02: 2 POLES
 03: 3 POLES

G:RoHS compliant(lead<4%)
 in copper alloy

MARK
 0: "@" MARK
 1: "ANY" MARK




TERMINAL & SCREW PLATED
 0: TERMINAL & SCREW: G/F
 1: TERMINAL: G/F, SCREW: Zinc
 2: TERMINAL: Sn, SCREW: G/F
 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-501 W/O Flange&With Cover Series (2P-3P)				
PART NO.	YK501xx2xx00G	DWG NO.		8YK0013-501		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.		Tolerance
		Guoxue 2014.06.11	Guoxue 2014.06.11			X. ±0.50
						X.X ±0.30
						X.XX ±0.10
SHEET: 01/01		REV.: B		X° ±1°		




N=Number of contacts

Dimension A&B

DIM A	N×9.5+3.0
DIM B	(N-1)×9.5

Poles	Tolerance
4P	±0.20
5P-10P	±0.30
11P-24P	±0.40
25P-30P	±0.60



MATERIALS ELECTRICAL	
RATED VOLTAGE & CURRENT:	300 V, 20 A
WITHSTAND VOLTAGE:	AC 2000 V/Min
INSULATION RESISTANCE:	1000 MΩ OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG:	-40 °C ~ +115 °C
SCREW TORQUE VALUE:	12 Lb-In.
WIRE RANGE:	22 - 12AWG
1) MOLDED PARTS:	THERMOPLASTIC, UL 94 V-0 BLACK
2) TERMINAL:	BRASS, 0.8t
3) TERMINAL SCREWS:	STEEL, M3.5
4) COVER MATERIAL:	PC

APPROVAL: 

Critical dimension: 

PART No.:

YK501 xx 2 x x 00G

NO. OF POLES
04: 4 POLES
05: 5 POLES
06: 6 POLES
:
30: 30 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK
0: "@" MARK
1: "ANY" MARK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F
1: TERMINAL: G/F, SCREW: Zinc
2: TERMINAL: Sn, SCREW: G/F
3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YK-501 W/O Flange&With Cover Series (4P-30P)						
PART NO.	YK501xx2xx00G			DWG NO.	8YK0002-501		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.	UNIT: mm SCALE: NONE SHEET: 01/01 REV.: E		Tolerance
		Airy min 2014.08.26	Airy min 2014.08.26				X. ±0.50
							X.X ±0.30
						X.XX ±0.10	
						X° ±1°	