







NOTES:

1. METAL SHELLS: STEEL; min. 320 μ " TIN
2. INSULATORS: PBT GF UL 94 V-0, GREEN
3. COAXIAL CONTACTS 50 OHM: COPPER ALLOY
PLATING: INNER CONDUCTOR: min. 50 μ " HARD GOLD OVER min. 50 μ " NICKEL
OUTER CONDUCTOR: min. 30 μ " TIN over 80 μ " NICKEL
4. METAL BRACKET: STEEL; min. 320 μ " TIN over 80 μ " NICKEL
5. THREADED INSERT: COPPER ALLOY; min. 200 μ " TIN over 80 μ " NICKEL
6. MAXIMUM TORQUE VALUE FOR THREAD: 6" LBS
7. CONNECTOR IS PART MARKED: 3008W8SXX78G20X CONEC Y/WW
8. = CRITICAL DIMENSION

used for: D-SUB COMBINATION

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GMBH
DO NOT ALTER CAD DRAWING BY HAND

tolerance		2:1 (5:1)	
scale:		material:	
title:		SEE NOTES	
2002	date	name	name
drawn	12.03.	Parel	
appd.	12.03.	E. Mickenbecker	
norm			
d-old			

D-SUB COMBINATION FEMALE 90°
8W8S

with threaded insert and metal bracket

dwg no: 13K1A503

AutoCAD 2000 DIN-A 3 sh:1/2

part no: 3008W8SXX78G20X

Directive 2002/95/EC
"RoHS"
Compliant

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

rev.	description	date	name



title: P.C.B. HOLE DRILLINGS D-SUB COMBINATION FEMALE 90° 8W8S with threaded insert and metal bracket

dwg no:	AutoCAD 2000	DIN-A
13K1A503		4
		sh:2/2

part no: SEE SHEET 1

