







N=Number of Poles

Dim A	$N \times 10.0 + 3.5$
Dim B	$(N-1) \times 10.0$

Poles	Tolerance	Dim A	Dim B
2p-3p		± 0.40	± 0.30



SIGN	DATE	DESCRIPTION	APPROVER
△	3/30'09	Temperature changed from -40 °105°C to -40 °115°C	JODY
△	11/17'12	Change the screw plating specification	Jacky
△	11/17'12	Change the dimensional tolerance	Jacky
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

MATERIALS ELECTRICAL

RATED VOLTAGE & CURRENT:

300 V, 20 A

WITHSTAND VOLTAGE:

AC 2000 V/Min

INSULATION RESISTANCE:

1000 MΩ OR MORE AT DC 500 V

OPERATING TEMPERATURE RANG:

△ -40 °C ~ +115 °C

SCREW TORQUE VALUE:

12Lb-In.

WIRE RANGE:

22 - 12 AWG

1) MOLDED PARTS:

POLYIMIDE 66, UL 94 V-0 BLACK

2) TERMINAL:

BRASS, 0.8t, Tin PLATED

△ 3) TERMINAL SCREWS:

STEEL, M3.5

4) COVER MATERIAL:

PC

APPROVAL: c  us

Critical dimension: 

PART No.:

YK 605 xx 2 x x 00G

NO. OF POLES

02: 2 POLES

03: 3 POLES

G:RoHS compliant(lead<4%)
in copper alloy

MARK

0: "@" MAK

1: "ANY" MAK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

△ 1: TERMINAL: G/F, SCREW: Zinc


2: TERMINAL: Sn, SCREW: G/F


△ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD




TITLE		YK-605 Without Flange Series, 2Pole & 3 Pole							
PART NO.		YK605xx2xx00G			DWG NO.	8YK0006-605			
APPROVED		CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance	
			Jacky 2012.11.17	Jacky 2012.11.17		UNIT: mm	X.	±0.50	
						SCALE: NONE	X.X	±0.30	
							X.XX	±0.10	
					SHEET: 01/01	REV: C	X°	±1°	



N=Number of Poles

Dim A	$N \times 10.0 + 3.5$
Dim B	$(N-1) \times 10.0$

Poles	Tolerance
4p-10p	± 0.40
11p-20p	± 0.60
21p-30p	± 0.80



MATERIALS ELECTRICAL
RATED VOLTAGE & CURRENT: 300 V, 20 A
WITHSTAND VOLTAGE: AC 2000 V/Min
INSULATION RESISTANCE: 1000 M Ω OR MORE AT DC 500 V
OPERATING TEMPERATURE RANG: Δ -40 °C ~ +115 °C
SCREW TORQUE VALUE: 12Lb-In.
WIRE RANGE: 22 - 12 AWG
1) MOLDED PARTS: POLYIMIDE 66, UL 94 V-0 BLACK
2) TERMINAL: BRASS, 0.8t, Tin PLATED
3) TERMINAL SCREWS: STEEL, M3.5
4) COVER MATERIAL: PC

APPROVAL: 
Critical dimension: 

PART No.:

YK 605 xx 2 x x 00G

NO. OF POLES

04: 4 POLES
05: 5 POLES
06: 6 POLES
...

30: 30 POLES

G: RoHS compliant (lead < 4%)
in copper alloy

MARK

0: "0" MAK

1: "ANY" MAK

TERMINAL & SCREW PLATED

0: TERMINAL & SCREW: G/F

Δ 1: TERMINAL: G/F, SCREW: Zinc


2: TERMINAL: Sn, SCREW: G/F

Δ 3: TERMINAL: Sn, SCREW: Zinc

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE		YK-605 Without Flange Series, 4-30 Pole					
PART NO.	YK605xx2xx00G			DWG NO.	8YK0001-605		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
		Airy min 2014.09.03	Airy min 2014.09.03		UNIT: mm		X. ±0.50
					SCALE: NONE		X.X ±0.30
							X.XX ±0.10
					SHEET: 01/01		REV.: E