





P.C.B LAYOUT



Dimension A&B

DIM A	$N/2 \times 5.08$
DIM B	$(N/2 - 1) \times 5.08$

N=Number of contacts

Poles	A&B Tolerance
2×2P-2×6P	±0.15
2×7P-2×12P	±0.25
2×13P-2×18P	±0.35
2×19P-2×24P	±0.40

△ YM xx 61 x 0 xxxx G

04	2x2 CONTACTS
06	2x3 CONTACTS
...	...
48	2x24 CONTACTS

- 0 Black
- 5 Green
- 6 Blue
- 8 Light Grey

0000:"@""Logo (Standard) Pb < 40,000ppm
000A:"ANYTEK""Logo (RoHS)
Any special item by
customer request,
please contact sales
department.

SIGN	DATE	DESCRIPTION	APPROVER
△	01/18/07	Soldering temperature changed from 245° to 250°	Tason
△	01/18/07	Part NO is Changed	Tason
△	11/11/11	Structure changed	ChenMing
△	11/11/11	The dimension is changed from 23.1 to 23	ChenMing
△	11/11/11	The dimension is changed from 0.5 to 0.6	ChenMing
△	11/11/11	The dimension is added	ChenMing
△	11/11/11	The dimension is changed from 16.2 to 16.5	ChenMing
△	11/11/11	The dimension is changed from 12.8 to 12.6	ChenMing

Material:

- Item 1 Terminal housing :Thermoplastic (UL 94V-0)
- Item 2 Clamp : Brass ,Ni plated
- Item 3 Wire guard solder pin : Brass ,Tin plated
- Item 4 Terminal screw: Steel Zinc plating"- "slot type

Electrical cULus

- Voltage rating: 300VAC
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-24
- Stranded wire(AWG): 12-24
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △ ● Soldering temperature: 250°C±10°C/5 Sec
- Safety Approval: us
- Critical dimension: 

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YM-5.08mm -R Series						
PART NO.	YMxx61x0xxxxG			DWG NO.	8YM0102		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			Tolerance
			ChenMing 2011.11.11		UNIT: mm	X.	±0.50
					SCALE: NONE	X.X	±0.30
				SHEET: 01/01	REV: E	X.XX	±0.10
						X°	±1°