








Directive 2002/95/EC
"RoHS"
Compliant

NOTES:

1. METAL SHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATOR: PBT GF UL 94 V-0; GREEN
3. HIGH POWER CONTACTS 10A: COPPER ALLOY
PLATING MATING AREA: 8µin HARD GOLD over min. 50µin NICKEL
PLATING TERMINATION SIDE: 8µin HARD GOLD over min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 16-20
4. CONNECTOR IS PART MARKED: 4005W5SXX61A10X CONEC ABC

APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	
CUSTOMER APPROVAL DATE:	
NAME:	TITLE:
COMPANY NAME:	
APPROVAL # FREIGABE # DEBLOCAGE # AUTORIZACION # APPROVAL	

THIS DRAWING MAY NOT BE COPIED OR
REPRODUCED IN ANY WAY, AND MAY NOT
BE PASSED ON TO A THIRD PARTY WITHOUT
WRITTEN PERMISSION.
OWNERSHIP AND COPYRIGHT OF CONEC GmbH

DO NOT ALTER CAD DRAWING BY HAND

rev.	description	date	name
a	Origin		

tolerance	dim. in mm	name
drawn	28.09.09	Lehmenkühler
appd.	28.09.09	Fischer
norm		
d-old		

CONEC

scale:	2:1 (5:1)
material:	SEE NOTES
title:	D-SUB COMBINATION FEMALE 5W5S SOLDER CUP for installation into water resistant hood
dwg no:	Inventor 10
part no:	4005W5SXX61A10X
DIN-A3	sh: 1