







Pin layout PCB 1,60mm/
Lochbild Leiterplatte 1,60mm



Technical specification:

Technische Daten:


Rated Voltage/ Bemessungsspannung: IEC 61076-2-101	250V
Current rating/ Strombelastbarkeit: IEC 61076-2-101	4 A / 40°C
Insulation resistance/ Isolationswiderstand: IEC 60512	>=100 MΩ
Pollution degree/ Verschmutzungsgrad: IEC 60664-1	3/2
Degree of protection/ Schutzart: IEC 60529	IP 67, in mated condition/ im verschraubten Zustand
Temperature range/ Umgebungstemperatur: EN 60512-11-10 EN 60512-11-4	-30°C ... +85°C -40°C -40°C ... +85°C
Mating cycles/ Steckzyklen: IEC 60512-9a	>=100

Materials/

Werkstoffe:

Contact/ Kontakt:	CuZn, Ni b / Au 0,2 gal.
Contact carrier/ Kontaktträger:	PA GF, UL 94 V-0
Sealing/ Dichtung:	NBR
Shroud/ Schirmblech:	CuSn, Ni / sel. Sn

Index: b Ä22-0209 06.07.2022 LTU



dim. in mm

**Insulating body female M12x1 angled,
D-coding, print contact**
*Isolierkörper Kupplung M12x1 gewinkelt,
D-Codiert, Printkontakt*

general tolerance/ Allgemeintoleranz:	0 ± 0,50mm 0,0 ± 0,25mm 0,00 ± 0,10mm A ± 1,5°
--	---

	Date/Datum	Name
drawn/ gez.	07.03.2018	Fromm
appd./ gepr.	07.03.2018	Schramm

Index: a Original	scale/Maßstab:
Status:	
RoHS & REACH compliant/konform	



dwg no /
Z.-nr.: 43K1A3945

DIN-
A4

1 / 2