

产 品 规 格 书

Product Specification

A2E200S-7KN-AAJ1轴流风机
(Single Phase Axial fan)
(220/230V 50/60Hz)

客户号 (Customer): _____

版 本 (Edition): A00

日 期 (Date): 2018.07.21

1.0 概述/ Introduction

本规格书主要描述了产品标准、使用环境、技术要求等。

This specification describes the standard、operation environment、and technic requirements of the product.

2.0 产品标准和安规要求/Requirement of production standard and safety regulations

2.1 本产品符合的标准 / The product satisfy requirements

2.1.1 GB12350 《小功率电动机的安全要求》

GB12350 《Safety requirments of small power motors》

2.1.2 GB/T13274-1991 《一般用途轴流风机通用技术条件要求》

GB/T13274-1991 《General technical requirement for general axial fan》

2.1.3 EN60335-1 《家电和类似用途电器的安全要求》

EN60335-1 《Household and similar electrical appliances-safety》

2.2 本产品通过 CCC、CE 认证


The fan has CCC、CE certificate

2.3 本产品全部材料符合RoHS要求

All material accord with RoHS.

3.0 机械要求/ Mechanical requirements

3.1 外形图/Dimension drawing



3.2 材质/Material

风轮冷轧板, 转子铸铝 ;

Impeller material: Steel, Rotor: Aluminum Casting;

3.3 电机/Motor

外转子交流电机/ External rotor AC motor

3.4 轴承

免维护滚珠轴承/ Maintenance free ball bearings

3.5 平衡/ Balancing

风机在额定电压和频率下运转时，每个端面动平衡精度不低于G6.3，符合标准JB/T9101。

At the rated voltage and frequency,,the residual unbalance of the fan is not less than G6.3(balancing precision grade) in each plane,according with JB/T9101.

3.6 振动/Vibration of the fan

风机振动速度有效值按照JB/T8689标准规定。

Vibration speed virtual value of fans accord with JB/T8689.

3.7 跳动/ Runout of impeller

风轮轴向、径向跳动 $\leq 3\text{mm}$ 。

Runout of impeller in axial and radial direction $\leq 3\text{mm}$ 。

3.8 使用寿命L10/Life time 10

风机寿命估算值63000小时，（在额定电压、环境温度为40℃、风机全速运转时）


Fan life expectance 63000 hours, determined when at nominal supply voltage,running at full speed, environment temperature of 40 ℃.

4.0 风机性能/Fan performance

4.1 性能参数/Performance data

	Voltage	Frequency	Current	Input Power	Speed	Capacitor	Air Flow	Noise	Operating Temperature	Curve No.	Approvals
Model No.	V	Hz	A	W	rpm	μF	m^3/h	dB(A)	Min / Max (℃)	#	
A2E200S-7KN-AAJ1	220/230	50	0.30	60	2550	2	880	53	-25 / +60	①	CCC , CE, RoHS
		60	0.34	75	2800		980	55		②	

4.2 特性曲线/Performance curve




5.0 电气性能/Electrical performance

5.1 铭牌/Label

☐ 中文/Chinese




☐ 英文/English




5.2 接线图/Wiring diagram

☐ 中文/Chinese



☐ 英文/English



5.3 电压范围/Voltage range

风机设计的额定运行电压为220V，可运行的电压范围是198~242V，

The fan is designed to operate at a nominal voltage of 220V, but can be operated in the AC supply voltage range of 198 to 242V.

5.4 保护/Protection

电机有热保护功能，断开温度:150—160℃, 复位温度:100—130℃

This motor with heat protection, cut off temperature:150—160℃, replacement temperature 100—130℃

5.5 防护等级/Type of protection

风机的防护等级为IP44。

Type of protection is IP44.

5.6 绝缘等级: F

Insulation Class: F

6.0 质量要求/Quality requests

质量要求符合ISO9001:2000 / Quality requests accord with ISO9001:2000

质量要求符合企业标准 / Quality requests accord with Airflow standard

7.0 使用和存储环境/ Operating and storing environment requirements

7.1 使用环境/ Operating environment requirements

使用温度范围/Operating temperatures from: $-25^{\circ}\text{C}\sim+60^{\circ}\text{C}$

使用湿度范围/Operating humidity from: 0%~95% RH

海拔高度/The altitude: $\leq 1000\text{m}$

7.2 贮存环境/Storing environment requirements

贮存温度范围: $-40^{\circ}\text{C}\sim+80^{\circ}\text{C}$, 贮存湿度范围: 0%~75% RH。

Storing temperatures from -40°C to $+80^{\circ}\text{C}$; Storing humidity from 0% to 75% RH.

8.0 包装和标识/ Packaging and marks

8.1 包装/Packaging

纸箱盒包装/Sheet chamber packaging

8.2 标识/Marks

制造商名称、产品型号、重量、尺寸等

Markings: Name of manufacturer, type of fan, date of manufacture, weight, Size etc.

9.0 附件/Other requirements on accessory

9.1 电容/Capacitor

■带/Yes, □不带/No, □根据销售订单配备/For Salers' request;

9.2 连接件要求/Annectent parts

端子/terminal(□有/Yes、■没有//No)