

FLK 14/16/EZ-DR/HF/ 250/S7 - Cable



2296951

<https://www.phoenixcontact.com/gb/products/2296951>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled, halogen-free round cable; controller: SIMATIC® TOP connect; connection 1: IDC/FLK socket strip (1x 16-position); connection 2: IDC/FLK socket strip (1x 14-position); cable length: 2.5 m

Commercial data

Item number	2296951
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	DK221S
Product key	DK221S
Catalog page	Page 525 (C-7-2015)
GTIN	4017918733643
Weight per piece (including packing)	137.7 g
Weight per piece (excluding packing)	130.4 g
Customs tariff number	85444290
Country of origin	DE

Technical data

Product properties

Product type	System cable
--------------	--------------

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP00
Degree of protection (Installation location)	≥ IP54 (Installation location)
Ambient temperature (operation)	-40 °C ... 70 °C (fixed installation) -10 °C ... 70 °C (flexible installation)
Ambient temperature (storage/transport)	-40 °C ... 80 °C
Altitude	≤ 2000 m

Electrical properties

Operating voltage (AC)	≤ 30 V AC
Operating voltage (DC)	≤ 60 V DC
Nominal operating mode	100% operating factor
Current (Per path, 50°C)	≤ 1 A (Uncoiled, see derating)
Current (Per path, 70°C)	≤ 0.6 A (Uncoiled, see derating)

Cable/line

Cable length	2.5 m
UL AWM Style	21946
Number of positions	14
Shielded	no
Conductor type	Assembled, halogen-free round cable
Conductor structure signal line	7x 0.16 mm
AWG signal line	26
Conductor cross section	14x 0.14 mm ²
Wire diameter incl. insulation	1 mm ±0.03 mm
External cable diameter	5.80 mm ±0.4 mm
Outer sheath, material	halogen-free (type 2)
External sheath, color	gray
Conductor material	Tin-plated Cu litz wires
Cable resistance	≤ 145 Ω/km (20 °C)
Insulation resistance	≥ 20 MΩ*km (20 °C)
Smallest bending radius, fixed installation	50 mm
Smallest bending radius, movable installation	93 mm
Dynamic load capacity (bending)	Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter)
Halogen-free	yes
	IEC 60332-1-2 (raw cable)

FLK 14/16/EZ-DR/HF/ 250/S7 - Cable



2296951

<https://www.phoenixcontact.com/gb/products/2296951>

Flame resistance	VDE 0842, Part 332-1-2 (raw cable) IEC 60332-3-22 (raw cable)
Resistance to oil	can withstand occasional splashes (raw cable)
Cable type	Cable for one module

Color code

white	IDC/FLK16 (1) = IDC/FLK14 (10)
violet	IDC/FLK16 (2) = IDC/FLK14 (8)
white-brown	IDC/FLK16 (3) = IDC/FLK14 (12)
blue	IDC/FLK16 (4) = IDC/FLK14 (7)
white-orange	IDC/FLK16 (5) = IDC/FLK14 (14)
green	IDC/FLK16 (6) = IDC/FLK14 (6)
yellow	IDC/FLK16 (8) = IDC/FLK14 (5)
gray	IDC/FLK16 (9) = IDC/FLK14 (9)
orange	IDC/FLK16 (10) = IDC/FLK14 (4)
white-black	IDC/FLK16 (11) = IDC/FLK14 (11)
red	IDC/FLK16 (12) = IDC/FLK14 (3)
white-red	IDC/FLK16 (13) = IDC/FLK14 (13)
brown	IDC/FLK16 (14) = IDC/FLK14 (2)
black	IDC/FLK16 (16) = IDC/FLK14 (1)

Connection data

Connection 1

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	16
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm

Connection 2

Connection in acc. with standard	IEC 60603-13 (in compliance)
Connection method	IDC/FLK socket strip
Number of connections	1
Number of positions	14
Insertion/withdrawal cycles	> 50
Pitch	2.54 mm


Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--


Drawings

Connection diagram		
14-pos. Socket strip PIN	16-pos. Socket strip PIN	Wire color
1	16	Black
2	14	Brown
3	12	Red
4	10	Orange
5	8	Yellow
6	6	Green
7	4	Blue
8	2	Violet
9	9	Gray
10	1	White
11	11	White-black
12	3	White-brown
13	13	White-red
14	5	White-orange
	7	-
	15	-


Pin assignment and color code



Maximum permissible current per path in uncoiled state



Pin assignment Siemens S7 front connector modules 6ES7 921-3...



Pin assignment of digital Siemens S7 front plug-in modules 6ES7 921-5AB20-0AA0 or 6ES7 921-5AH20-0AA0

FLK 14/16/EZ-DR/HF/ 250/S7 - Cable



2296951

<https://www.phoenixcontact.com/gb/products/2296951>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2296951>



EAC

Approval ID: RU*-DE.HB*35.B00385



UL Listed

Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-



cUL Listed

Approval ID: E238705

	Nominal voltage U_N	Nominal current I_N	Cross section AWG	Cross section mm^2
	125 V	1 A	-	-

FLK 14/16/EZ-DR/HF/ 250/S7 - Cable



2296951

<https://www.phoenixcontact.com/gb/products/2296951>

Classifications

ECLASS

ECLASS-13.0	27242220
-------------	----------

ETIM

ETIM 9.0	EC000237
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

FLK 14/16/EZ-DR/HF/ 250/S7 - Cable



2296951

<https://www.phoenixcontact.com/gb/products/2296951>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2025 © - all rights reserved
<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd
Halesfield 13, Telford
Shropshire, TF7 4PG
01952 681700
info@phoenixcontact.co.uk