

RFPC-SMA27-F : SMA Right Angle Jack, PCB Connector, 6GHz

Material and Plating:

Insulator: PTFE

Pin: Brass, Gold



Body: Brass, Gold

Specification:


Operating Temperature: -55°C~+125°C

Working Frequency Range: DC~6GHz

Impedance: 50 Ohm.



Recommended PCB Layout
Tolerance:±0.05




REV. DATE & DRN
1.0 17/07/23 - CC RELEASE
1.1 29/03/24 - CC RELEASE Update product description
1.2 12/05/25 - NYW Add GCT logo.

Scale: NTS	THIRD ANGLE	Unstated .X .XX .XXX ANGLES	Tolerances: ±0.2 ±0.1 ±0.05 ±3°	Material SEE NOTE
Drawn: CC				
App'd: XXX	Title SMA PCB Connector	NOT TO SCALE		
Date: 12 MAY '25	Revision: 1.2	Unit: mm		



© THIS DRAWING IS CONFIDENTIAL AND MUST NOT BE
COPIED OR DISCLOSED WITHOUT WRITTEN CONSENT

Type: RFPC-SMA27-F
RFPC-SMA27-F
Drawing Number:
Sheet 1 of 2
Drawing © E and O E



pcs / Tray	Trays / Carton	pcs/Carton
100	30	3000