

N-channel 250V 295mΩ Power MOSFET

Description



WMOSTM JN is suitable for applications which require superior power density and outstanding efficiency.

Features

- Gate charge minimized
- Typ. $R_{DS(on)} = 295\text{ m}\Omega$
- 100% UIS tested
- Pb-free plating, Halogen free

Applications

Switching applications



PDFN 5x6

Absolute Maximum Ratings

Parameter	Symbol	WMx09N25JN	WML09N25JN	Unit
Drain-source voltage	V_{DSS}	250		V
Continuous drain current ¹⁾ ($T_C = 25^\circ\text{C}$)	I_D	7		A
		4.2		A
($T_C = 100^\circ\text{C}$)				
Pulsed drain current ²⁾	I_{DM}	21		A
Gate-source voltage	V_{GS}	± 20		V
Avalanche energy, single pulse ³⁾	E_{AS}	17		mJ
Avalanche energy, repetitive ²⁾	E_{AR}	0.1		mJ
Avalanche current, repetitive ²⁾	I_{AR}	0.7		A
Power dissipation ($T_C = 25^\circ\text{C}$)	P_D	31	17	W
		0.25	0.14	W/ $^\circ\text{C}$
- Derate above 25°C				
Operating and storage temperature range	$T_{j, T_{stg}}$	-55 to +150		$^\circ\text{C}$
Continuous diode forward current	I_S	7		A
Diode pulse current	$I_{S,pulse}$	21		A

Thermal Characteristics

Parameter	Symbol	WMx09N25JN	WML09N25JN	Unit
Thermal resistance, junction-to-case	$R_{\theta JC}$	4	7	$^\circ\text{C/W}$
Thermal resistance, junction-to-ambient	$R_{\theta JA}$	62	80	$^\circ\text{C/W}$

Electrical Characteristics T_c = 25°C, unless otherwise noted

Parameter	Symbol	Test Condition	Min.	Typ.	Max.	Unit
Static characteristics						
Drain-source breakdown voltage	BV _{DSS}	V _{GS} =0 V, I _D =1 mA	250	-	-	V
Gate threshold voltage	V _{GS(th)}	V _{DS} =V _{GS} , I _D =0.25mA	2.5	3.5	4.5	V
Drain cut-off current	I _{DSS}	V _{DS} =250 V, V _{GS} =0V, T _J = 25°C T _J = 125°C	- -	- 30	1 -	μA
Gate leakage current, forward	I _{GSSF}	V _{GS} =20V, V _{DS} =0V	-	-	500	nA
Drain-source on-state resistance	R _{DS(on)}	V _{GS} =10 V, I _D =3A T _J = 25°C	- -	 295	 360	 mΩ
Dynamic characteristics						
Input capacitance	C _{iss}	V _{DS} = 100V, V _{GS} = 0V, f = 1 MHz	-	191	-	pF
Output capacitance	C _{oss}		-	8	-	
Reverse transfer capacitance	C _{rss}		-	0.4	-	
Turn-on delay time	t _{d(on)}	V _{DD} = 100V, I _D = 3A R _G = 4.7Ω, V _{GS} =10V	-	3	-	ns
Rise time	t _r		-	4	-	
Turn-off delay time	t _{d(off)}		-	8	-	
Fall time	t _f		-	3	-	
Gate charge characteristics						
Gate to source charge	Q _{gs}	V _{DD} =160V, I _D =3A, V _{GS} =0 to 10V	-	1.7	-	nC
Gate to drain charge	Q _{gd}		-	0.8	-	
Gate charge total	Q _g		-	3.9	-	
Gate plateau voltage	V _{plateau}		-	5.5	-	V
Reverse diode characteristics						
Diode forward voltage	V _{SD}	V _{GS} =0 V, I _F =3A	-	-	1.2	V
Reverse recovery time	t _{rr}	V _R =50V, I _F =3A, dI _F /dt=100A/μs	-	75	-	ns
Reverse recovery charge	Q _{rr}		-	0.2	-	μC
Peak reverse recovery current	I _{rrm}		-	5.7	-	A

Notes:

- Limited by T_{j max}. Maximum duty cycle D=0.5.
- Repetitive rating: pulse width limited by maximum junction temperature.
- I_{AS} = 0.7A, V_{DD} = 50V, R_G = 25Ω, starting T_j = 25°C.




Figure 1. On-Region Characteristics




Figure 2. Transfer Characteristics




Figure 3. Static Drain-Source On Resistance






Figure 4. Body-Diode Forward Characteristics

Figure 5. Normalized BV_{DS} vs. TemperatureFigure 6. Normalized $R_{DS(on)}$ vs. Temperature




Figure 7. Threshold Voltage vs. Temperature




Figure 8. Capacitance Characteristics




Figure 9. Power Dissipation




Figure 10. Power Dissipation (TO-220F)




Figure 11. Maximum Safe Operating Area




Figure 12. Maximum Safe Operating Area(TO-220F)




Figure 13. Transient Thermal Response Curve (TO-220F)




Figure 14. Transient Thermal Response Curve






Figure 15. Gate Charge Characteristics


Gate Charge Test Circuit & Waveform




Switching Test Circuit & Waveforms



Unclamped Inductive Switching Test Circuit & Waveforms



Mechanical Dimensions for TO-220F




COMMON DIMENSIONS

SYMBOL	MM	
	MIN	MAX
A	9.96	10.36
B	15.10	16.10
C	3.03	3.38
D	12.64	13.28
E	1.18	1.58
F	0.70	0.95
G	2.54REF	
H	4.50	4.90
I	2.34	2.74
J	15.57	16.17
K	6.70REF	
L	2.56	2.96
M	0.40	0.65
L1	2.85	3.45

Mechanical Dimensions for PDFN 5x6


COMMON DIMENSIONS



SYMBOL	MM	
	MIN	MAX
A	0.9	1.2
b	0.25	0.51
C	0.15	0.35
D1	4.8	5.4
D2	3.7	4.4
E1	5.95	6.35
E2	5.65	6.06
E4	3.3	3.92
e	1.17	1.37
H	0.38	0.71
K	1.1	1.6
L	0.3	0.71
L1		0.12

Mechanical Dimensions for TO-263


COMMON DIMENSIONS



SYMBOL	MM	
	MIN	MAX
A	4.37	4.89
A1	1.17	1.42
A2	2.19	2.89
b	0.70	0.96
b1	1.17	1.47
c	0.30	0.60
D1	8.45	9.35
D4	6.60	—
E	9.80	10.40
E5	7.06	—
e	2.54BSC	
H	14.70	16.00
H2	1.07	1.47
L	2.00	2.70
L1	1.15	1.75
L4	0.25BSC	
θ	0°	9°

Mechanical Dimensions for TO-262


COMMON DIMENSIONS




SYMBOL	MM	
	MIN	MAX
A	4.37	4.90
A1	1.17	1.42
A2	2.49	2.89
b	0.71	0.96
b2	1.07	1.47
c	0.28	0.53
D	23.20	24.02
D1	8.45	8.90
D2	6.00	—
E1	9.86	10.40
E4	7.06	—
e	2.54BSC	
G	1.25	1.50
H2	—	1.50
L	13.33	14.16
L1	3.50	4.00
L3	1.28	1.58

Mechanical Dimensions for TO-220

COMMON DIMENSIONS




SYMBOL	MM	
	MIN	MAX
A	9.70	10.30
B	3.40	3.80
C	8.80	9.40
D	1.17	1.47
E	2.60	3.50
F	15.10	16.90
G	19.60MAX	
H	2.54REF	
I	0.70	0.95
J	9.25	11.00
K	4.30	4.77
L	1.20	1.45
M	0.40	0.65
N	2.20	2.60

Mechanical Dimensions for TO-252

COMMON DIMENSIONS

SYMBOL	MM	
	MIN	MAX
A	6.40	6.80
B	5.13	5.50
C	0.88	1.28
D	5.90	6.22
E	0.68	1.10
F	0.68	0.91
G	2.29REF	
H	2.90REF	
I	0.85	1.17
J	0.51REF	
K	2.10	2.50
L	0.40	1.00

Mechanical Dimensions for TO-251




COMMON DIMENSIONS

SYMBOL	MM	
	MIN	MAX
A	6.40	6.80
B	5.13	5.50
C	0.88	1.28
D	5.90	6.22
E	0.68	1.10
F	0.68	0.91
G	2.29REF	
H	9.00	9.65
I	0.85	1.17
J	0.40	0.61
K	2.10	2.50

Ordering Information

Part	Package	Marking	Packing method
WML09N25JN	TO-220F	WML09N25JN	Tube
WMK09N25JN	TO-220	WMK09N25JN	Tube
WMN09N25JN	TO-262	WMN09N25JN	Tube
WMM09N25JN	TO-263	WMM09N25JN	Tape and Reel
WMO09N25JN	TO-252	WMO09N25JN	Tape and Reel
WMB09N25JN	PDFN 5x6	WMB09N25JN	Tape and Reel
WMP09N25JN	TO-251	WMP09N25JN	Tube

Marking Information



Contact Information

No.1001, Shiwan(7) Road, Pudong District, Shanghai, P.R.China.201202

Tel: 86-21-50310888 Fax: 86-21-50757680 Email: market@way-on.com

WAYON website: <http://www.way-on.com>

For additional information, please contact your local Sales Representative.

® is registered trademarks of Wayon Corporation.

Disclaimer

WAYON reserves the right to make changes without further notice to any Products herein to improve reliability, function, or design. The Products are not designed for use in hostile environments, including, without limitation, aircraft, nuclear power generation, medical appliances, and devices or systems in which malfunction of any Product can reasonably be expected to result in a personal injury. The information given in this document shall in no event be regarded as a guarantee of conditions or characteristics. WAYON does not assume any liability for infringement of patents, copyrights, or other intellectual property rights of third parties by or arising from the use of Products or technical information described in this document.