




SPL (HONG KONG) LIMITED
香港九龍觀塘鴻圖道57號南洋廣場17樓1703B室
Room 1703B, 17/F., Nanyang Plaza, No.57 Hung To Road, Kwun Tong, Kowloon, HK.
Tel: 852-2342 6857 / 2342 6867 Fax: 852-2342 6847 Email: sales@spl-hk.com.hk
Website: www.buzzer.com.hk

External Drive Piezo Transducer SPT07 series

DIMENSIONS

Date : 14 May, 2025



Ref No. : PBEE1402A



ELECTRICAL SPECIFICATIONS

Model No.	PT07-220740HPYR
Sound Pressure Level	80 dBA min. [3 Vp-p, sine wave, 10cm, 4000Hz]
Capacitance	28000pF $\pm$ 40% at 120Hz
Max. Input Voltage	30 Vp-p
Heat Test	Must Be Normal [88 $\pm$ 2 $^{\circ}$ C, 24 Hours]
Cold Test	Must Be Normal [-30 $\pm$ 2 $^{\circ}$ C, 24 Hours]
Humidity Test	40 $\pm$ 3 $^{\circ}$ C, 90 ~ 95% R.H. 24 Hours
Operating Temperature $^{\circ}$ C	-20 ~ +70
Storage Temperature $^{\circ}$ C	-30 ~ +88
Terminal	Pin
Housing Material	PBT
Colour	Black
Weight [gm]	Approx. 2