


IGBT MODULE 2-PACK TYPE**Features**

- $I_c=75A$
- Ultrafast switching speed
- Excellent short circuit ruggedness
- Low conduction loss

**Typical Applications**

- IGBTs offer ultrafast switching speed for application such as Welding, inductive heating, UPS and other high frequency Application.

Absolute Maximum Ratings

V_{CES}	Collector to Emitter Voltage		1200	V
V_{GES}	Continuous Gate to Emiiter Voltage		+/-30	V
I_C	Continuous Collector Current	$T_C=25^{\circ}C$	150	A
		$T_C=100^{\circ}C$	75	
I_{CM}	Pulse Collector Current	$T_J=150^{\circ}C$	150	A
P_D	Maximum Power Dissipation(IGBT)	$T_C=25^{\circ}C$	320	W
t_{sc}	Short Circuit Withstand Time		> 10	μs
T_J	Maximum IGBT Junction Temperature		-40~+150	$^{\circ}C$
T_{JOP}	Maximum Operating Junction temperature Rang		-40~+150	$^{\circ}C$
T_{stg}	Storage Temperature Range		-40~+125	$^{\circ}C$

Electrical Characteristics at T_J=25°C (Unless Otherwise Specified)

Parameter	Test Condition	Min.	Typ.	Max.	Unit
BV _{CES}	Collector to Emitter Breakdown Voltage	V _{GE} =0V, I _C =1mA	600/1200		V
I _{CES}	Collector to Emitter Leakage Current	V _{GE} =0V, V _{CE} = V _{CES}		1	mA
I _{GES}	Gate to Emitter Leakage Current	V _{GE} =+/-30V, V _{CE} =0V		200	nA
V _{GE(th)}	Gate Threshold Voltage	I _C =1mA, V _{CE} =V _{GE}	4.5	5.7	V
V _{CE(sat)}	Collector to Emitter Saturation Voltage (Module Level)	I _C =75A T _J =25°C V _{GE} =15V	2.3	2.5	V


Switching Characteristics

td(on)	Turn-on Delay Time	V _{CC} =600V I _C =75A R _G =10Ω V _{GE} =+/-15V Inductive Load	T _J =25°C		20		ns
			T _J =125°C		25		
tr	Turn-on Rise Time		T _J =25°C		30		ns
			T _J =125°C		40		
td(off)	Turn-off Delay Time		T _J =25°C		230		ns
			T _J =125°C		240		
tf	Turn-off Fall Time		T _J =25°C		110		ns
			T _J =125°C		190		
E _{on}	Turn-on Switching Loss		T _J =25°C		3.4		mJ
			T _J =125°C		4.3		
E _{off}	Turn-off Switching Loss		T _J =25°C		1.9		mJ
			T _J =125°C		3.4		
Q _g	Total Gate Charge		T _J =25°C		500		nC
R _{gint}	Integrated Gate Resistor	f=1M, V _{pp} =1V	T _J =25°C		2.3		Ω
C _{ies}	Input Capacitance	V _{CE} =25V V _{GE} =0V f=1MHZ	T _J =25°C		5.2		nF
C _{oes}	Output Capacitance		T _J =25°C		0.69		
C _{res}	Reverse Transfer capacitance		T _J =25°C		0.45		
R _{jc}	Thermal Resistance, Junction-to-Case					0.20	°C/W

Module Characteristics

Parameter		Min.	Typ.	Max.	Unit
V _{iso}	Isolation Voltage(All terminals Shorted) f=50Hz, 1Minute	2500		3000	V
R _{cs}	Case-to-Sink(Conductive Grease Applied)		0.1		°C/W
M	Power Terminals Screw M5	3.0		5.0	Nm
M	Mounting Screw M6	4.0		6.0	Nm
G	Weight		155		g

Internal Circuit:



Package Dimension in Millimeter

