



SPL (HONG KONG) LIMITED


香港九龍觀塘鴻圖道57號南洋廣場17樓1703B室
Room 1703B, 17/F., Nanyang Plaza, No.57 Hung To Road, Kwun Tong, Kowloon, HK.
Tel: 852-2342 6857 / 2342 6867 Fax: 852-2342 6847 Email: sales@spl-hk.com.hk
Website: www.buzzer.com.hk

External Drive Piezo Transducer

SPT14 series

DIMENSIONS

Date : 15 May, 2025



Ref No. : PBCF2007C



ELECTRICAL SPECIFICATIONS

Model No.	PT14-221240HPYR
Sound Pressure Level	85 dBA min. [5V p-p, square wave, 10cm, 4000Hz]
Capacitance	25000pF $\pm$ 30% at 120Hz
Max. Input Voltage	20 Vp-p
Heat Test	Must Be Normal [85 $\pm$ 3 $^{\circ}$ C, 24 Hours]
Cold Test	Must Be Normal [-40 $\pm$ 3 $^{\circ}$ C, 24 Hours]
Humidity Test	40 $\pm$ 3 $^{\circ}$ C, 92 ~ 95% R.H. 24 Hours
Operating Temperature [$^{\circ}$ C]	-40 ~ +85
Storage Temperature [$^{\circ}$ C]	-40 ~ +85
Terminal	Pin
Housing Material	PBT
Colour	Black
Weight [gm]	Approx. 2.9