


SMF



Automotive grade 200 W Transient voltage suppressor



Product features

- Automotive grade (AEC-Q101 qualified)
- Low profile SOD-123FL package
- Excellent clamping capability
- High reliability application
- 200 W peak pulse power capability at 10/1000 μ s waveform
- Typical I_R less than 1 μ A above 6 V
- Fast response time: typically less than 1.0 ps from 0 V to V_{BR} minimum
- Plastic package meets UL 94 V-0 flammability rating
- Meets moisture sensitivity level (MSL) level 1
- Terminal: tin plated, solderable per J-STD-002

PIN configuration



Applications

- Automotive chassis and safety systems
- Advanced driver assistance systems (ADAS)
- Communication and infotainment systems
- Network systems and body electronics
- Power train controls
- xEV and battery systems

Environmental compliance and general specifications

- AEC-Q101 qualified



Ordering part number

	SMF	5.0	C	A	H
Family name					
V_R voltage					
Bi-/Uni-Directional (Blank=Uni, C=Bi)					
Voltage tolerance					
High reliability application					

Alternate ordering part number


	SMFE	5-0	C	A	H
Family name					
V_R voltage ("-" indicates decimal point)					
Bi-/Uni-Directional (Blank=Uni, C=Bi)					
Voltage tolerance					
High reliability application					

Absolute maximum ratings

(+25 °C, RH=45%-75%, unless otherwise noted)


Parameter	Symbol	Value	Unit
Storage operating junction temperature range	T_{STG}/T_J	-55 to +150	°C
Peak pulse power dissipation on 10/1000 μ s waveform	P_{PP}	200	W
Maximum instantaneous forward voltage at 20 A for unidirectional	V_F	3.5	V
Typical thermal resistance junction to lead	$R_{\theta JL}$	100	°C/W
Typical thermal resistance junction to ambient	$R_{\theta JA}$	220	°C/W

Mechanical parameters, pad layout- mm/inches



Dimension	Millimeters		Inches	
	Minimum	Maximum	Minimum	Maximum
A	2.60	3.00	0.102	0.118
B	1.60	2.00	0.063	0.079
C	3.45	3.95	0.136	0.156
D	0.10	0.25	0.004	0.010
E	0.30	0.90	0.012	0.035
F	0.80	1.20	0.031	0.047
G	0.70	1.00	0.0275	• 0.0393
J	1.30	-	0.051	-
K	-	1.70	-	0.067
L	1.30	-	0.051	-

Part marking




Cathode band (uni-polar only)
Part marking:
yyyy= Placeholder- refer to "Marking" listed in
Electrical characteristics table for actual marking

Packaging information - mm/inches

Drawing not to scale.

Supplied in tape and reel packaging, 3,000 parts per 7" diameter reel (EIA-481 compliant)



Dimensions	Millimeters	Inches
A0	1.95 ± 0.3	0.077 ± 0.012
B0	3.95 ± 0.3	0.156 ± 0.012
C	178	7.0
D0	1.55 ± 0.1	0.061 ± 0.004
E1	1.75 ± 0.2	0.069 ± 0.008
F	3.50 ± 0.2	0.138 ± 0.008
P0	4.00 ± 0.2	0.157 ± 0.008
P1	4.00 ± 0.2	0.157 ± 0.008
P2	2.00 ± 0.2	0.079 ± 0.008
W	8.0 ± 0.2	0.315 ± 0.008
W1	11.5 ± 1.0	0.453 ± 0.039


Electrical specifications (+25 °C)

Part number		Marking		V _R	I _R @ V _R	V _{BR} @ I _T		I _T	V _C @ I _{PP}	I _{PP}
Uni-polar	Bi-polar	Uni	Bi	(V)	max (μA)	min (V)	max (V)	(mA)	max (V)	(A)
SMF5.0AH	/	KEH	/	5	10	6.4	7	10	9.2	21.7
SMF6.0AH	/	KGH	/	6	10	6.67	7.37	10	10.3	19.4
/	SMF5.0CAH	/	5CH	5	40	6.4	7	10	9.2	21.7
/	SMF6.0CAH	/	6CH	6	40	6.67	7.37	10	10.3	19.4
SMF10AH	SMF10CAH	KXH	10CH	10	1	11.1	12.3	1	17	11.8
SMF11AH	SMF11CAH	KZH	11CH	11	1	12.2	13.5	1	18.2	11
SMF12AH	SMF12CAH	LEH	12CH	12	1	13.3	14.7	1	19.9	10.1
SMF13AH	SMF13CAH	LGH	13CH	13	1	14.4	15.9	1	21.5	9.3
SMF14AH	SMF14CAH	LKH	14CH	14	1	15.6	17.2	1	23.2	8.6
SMF15AH	SMF15CAH	LMH	15CH	15	1	16.7	18.5	1	24.4	8.2
SMF16AH	SMF16CAH	LPH	16CH	16	1	17.8	19.7	1	26	7.7
SMF17AH	SMF17CAH	LRH	17CH	17	1	18.9	20.9	1	27.6	7.2
SMF18AH	SMF18CAH	LTH	18CH	18	1	20	22.1	1	29.2	6.8
SMF20AH	SMF20CAH	LVH	20CH	20	1	22.2	24.5	1	32.4	6.2
SMF22AH	SMF22CAH	LXH	22CH	22	1	24.4	26.9	1	35.5	5.6
SMF24AH	SMF24CAH	LZH	24CH	24	1	26.7	29.5	1	38.9	5.1
SMF26AH	SMF26CAH	MEH	26CH	26	1	28.9	31.9	1	42.1	4.8
SMF28AH	SMF28CAH	MGH	28CH	28	1	31.1	34.4	1	45.4	4.4
SMF30AH	SMF30CAH	MKH	30CH	30	1	33.3	36.8	1	48.4	4.1
SMF33AH	SMF33CAH	MMH	33CH	33	1	36.7	40.6	1	53.3	3.8
SMF36AH	SMF36CAH	MPH	36CH	36	1	40	44.2	1	58.1	3.4
SMF40AH	SMF40CAH	MRH	40CH	40	1	44.4	49.1	1	64.5	3.1
SMF43AH	SMF43CAH	MTH	43CH	43	1	47.8	52.8	1	69.4	2.8
SMF45AH	SMF45CAH	MVH	45CH	45	1	50	55.3	1	72.7	2.7
SMF48AH	SMF48CAH	MXH	48CH	48	1	53.3	58.9	1	77.4	2.6
SMF51AH	SMF51CAH	MZH	51CH	51	1	56.7	62.7	1	82.4	2.4
SMF54AH	SMF54CAH	NEH	54CH	54	1	60	66.3	1	87.1	2.3
SMF58AH	SMF58CAH	NGH	58CH	58	1	64.4	71.2	1	93.6	2.1
SMF60AH	SMF60CAH	NKH	60CH	60	1	66.7	73.7	1	96.8	2
SMF64AH	SMF64CAH	NMH	64CH	64	1	71.1	78.6	1	103	1.9
SMF70AH	SMF70CAH	NPH	70CH	70	1	77.8	86	1	113	1.8
SMF75AH	SMF75CAH	NRH	75CH	75	1	83.3	92.1	1	121	1.7
SMF78AH	SMF78CAH	NVH	78CH	78	1	86.7	95.8	1	126	1.6
SMF85AH	SMF85CAH	NXH	85CH	85	1	94.4	104	1	137	1.5
SMF90AH	SMF90CAH	NZH	90CH	90	1	100	111	1	146	1.4
SMF100AH	SMF100CAH	PEH	100CH	100	1	111	123	1	162	1.2
SMF110AH	SMF110CAH	PGH	110CH	110	1	122	135	1	177	1.1
SMF120AH	SMF120CAH	PKH	120CH	120	1	133	147	1	193	1
SMF130AH	SMF130CAH	PMH	130CH	130	1	144	159	1	209	0.9
SMF150AH	SMF150CAH	PRH	150CH	150	1	167	185	1	243	0.8
SMF160AH	SMF160CAH	PVH	160CH	160	1	178	197	1	259	0.8
SMF170AH	SMF170CAH	PXH	170CH	170	1	189	209	1	275	0.7
SMF180AH	SMF180CAH	PZH	180CH	180	1	201	222	1	292	0.7
SMF200AH	SMF200CAH	QEH	200CH	200	1	224	247	1	324	0.6
SMF220AH	SMF220CAH	QRH	220CH	220	1	246	272	1	356	0.5


Note: Standard part numbers listed. Alternate part numbers have the addition of an E and a “-” for the “.” where applicable. Example standard part number SMF5.0AH, Alternate part number SMF5E-0AH

Ratings and V-I characteristic curves (+25 °C unless otherwise noted)

V- I curve characteristics (Uni-directional)



V- I curve characteristics (Bi-directional)



Surge waveform: 10/1000 μ s

V_R : Stand-off voltage – Maximum voltage that can be applied

V_{BR} : Breakdown voltage


V_C : Clamping voltage – Peak voltage measured across the suppressor at a specified I_{PP}

I_R : Reverse leakage current


I_T : Test current

V_F : Forward voltage drop for Uni-directional

Pulse waveform



Pulse derating curve



Solder reflow profile



Table 1 - Standard SnPb solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ ≥350
<2.5 mm	235 °C	220 °C
≥2.5 mm	220 °C	220 °C

Table 2 - Lead (Pb) free solder (T_C)

Package thickness	Volume mm ³ <350	Volume mm ³ 350 - 2000	Volume mm ³ >2000
<1.6 mm	260 °C	260 °C	260 °C
1.6 – 2.5 mm	260 °C	250 °C	245 °C
>2.5 mm	250 °C	245 °C	245 °C

Reference J-STD-020

Profile feature	Standard SnPb solder	Lead (Pb) free solder
Preheat and soak		
• Temperature min. (T_{smin})	100 °C	150 °C
• Temperature max. (T_{smax})	150 °C	200 °C
• Time (T_{smin} to T_{smax}) (t_s)	60-120 seconds	60 - 180 seconds
Ramp up rate T_L to T_p	3 °C/ second max.	3 °C/ second max.
Liquidous temperature (T_L)	183 °C	217 °C
Time (t_L) maintained above T_L	60-150 seconds	60-150 seconds
Peak package body temperature (T_p)*	Table 1	Table 2 (+0, -5 °C)
Time (t_p)* within 5 °C of the specified classification temperature (T_C)	20 seconds*	40 seconds*
Ramp-down rate (T_p to T_L)	6 °C/ second max.	6 °C/ second max.
Time 25 °C to peak temperature	6 minutes max.	8 minutes max.

* Tolerance for peak profile temperature (T_p) is defined as a supplier minimum and a user maximum.

Life Support Policy: Eaton does not authorize the use of any of its products for use in life support devices or systems without the express written approval of an officer of the Company. Life support systems are devices which support or sustain life, and whose failure to perform, when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in significant injury to the user.

Eaton reserves the right, without notice, to change design or construction of any products and to discontinue or limit distribution of any products. Eaton also reserves the right to change or update, without notice, any technical information contained in this bulletin.

Eaton
Electronics Division
1000 Eaton Boulevard
Cleveland, OH 44122
United States
Eaton.com/electronics

© 2024 Eaton
All Rights Reserved
Printed in USA
Publication No. ELX1066
September 2024

Eaton is a registered trademark.

All other trademarks are property of their respective owners.

Follow us on social media to get the latest product and support information.

