




SPL (HONG KONG) LIMITED
香港九龍觀塘鴻圖道57號南洋廣場17樓1703B室
Room 1703B, 17/F., Nanyang Plaza, No.57 Hung To Road, Kwun Tong, Kowloon, HK.
Tel: 852-2342 6857 / 2342 6867 Fax: 852-2342 6847 Email: sales@spl-hk.com.hk
Website: www.buzzer.com.hk

External Drive Piezo Transducer SPT93 series

DIMENSIONS

Date : 15 May, 2025



Ref No. : PBEE1406B



ELECTRICAL SPECIFICATIONS

Model No.	PT93-180820PMYR
Sound Pressure Level	90 dBA min. [12 Vp-p square wave, 10cm, 2000Hz]
Capacitance	25000 pF +/- 30% at 100Hz
Max. Input Voltage	18 Vp-p
Heat Test	Must Be Normal [105 +/- 3 °C, 24 Hours]
Cold Test	Must Be Normal [-40 +/- 3 °C, 24 Hours]
Humidity Test	40 +/- 3 °C, 92 ~ 95% R.H. 24 Hours
Operating Temperature	[°C] -40 ~ +105
Storage Temperature	[°C] -40 ~ +105
Terminal	PPS
Housing Material	SMD
Colour	Black
Weight	[gm] Approx. 3 g